
Part Number : WGA122SAD11SYLFM342
Product Description : AirBorn W Series Rectangular Board Mount Receptacle with Socket Contacts, Vertical, Through Hole, 3 Rows, 0.100"/2.54mm Pitch, 0.172" Tail Length, Plastic Body, Guide Set Reversed, with Mounting Ears, 122 Circuits
Status : Active
Product Category : Board-to-Board Connectors



Documents and Resources

Specifications

Materials Specification

Performance Specification

Solder Cup Adapter Sleeve, Coax Removal Tool, Extension Nuts

Nut Spanner Wrenches, Insertion & Removal Tools, Crimp Tools & Positioners

Contacts (WT, WTA, WTB, WTK, WG, WGA)

Hardware Availability (pg 1)

Hardware Availability (pg 2)

Polarizing Pin Applications

Face Seal Gaskets (WG-WGA-WGE Series)

Dimensional Information

Part Number Buildup

Part Details

General

Status	Active
Category	Board-to-Board Connectors
Description	AirBorn W Series Rectangular Board Mount Receptacle with Socket Contacts, Vertical, Through Hole, 3 Rows, 0.100"/2.54mm Pitch, 0.172" Tail Length, Plastic Body, Guide Set

Downloaded from Arrow.com.

	Reversed, with Mounting Ears, 122 Circuits
Application	Board-to-Board, Wire-to-Board
Comments	Socket, Straight, Through Hole, .172" x .027" dia; Remove mounting Ears, (250" each end)
Component Type	Receptacle
Contact Type	Socket
Product Name	AirBorn W Series
Series	W Series

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	1000V

Physical

Breakaway	No
Circuits (Loaded)	122
Circuits (maximum)	122
Color - Resin	Gray
Durability (mating cycles max)	500
Glow-Wire Capable	No
Guide to Mating Part	Guide Set, Reversed
Keying to Mating Part	No
Lock to Mating Part	No
Material - Plating Mating	Gold
Material - Shell	Polyphenylene Sulfide
Number of Rows	3
Orientation	Vertical
Packaging Type	Tray
PCB Retention	Yes
PC Tail Length	0.172"
Pitch - Mating Interface	0.100" (2.54mm)
Pitch - Termination Interface	0.100" (2.54mm)
Plating min - Mating	50µ”
Polarized to Mating Part	No

Downloaded from Arrow.com.

Stackable	No
Temperature Range - Operating	-65° to +125°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description
Rectangular, Plastic, 3 Row, Right Angle Board or Cable Mount Plug
Rectangular, Plastic, 3 Row, Vertical Board or Cable Mount Plug

Downloaded from Arrow.com.