

Part Number : 1202310038
Product Description : Brad M23 Signal Connector, Front Panel-Mount Receptacle, Straight Male Flange Mount 4xØ 3.20mm, Crimp Contacts, 17 Poles
Series Number : 120231
Status : Obsolete
Product Category : Industrial Connectors
Engineering Part Number : KRSJG26-0131

Documents and Resources

Drawings

1202310038_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Industrial Connectors
Series	120231
Description	Brad M23 Signal Connector, Front Panel-Mount Receptacle, Straight Male Flange Mount 4xØ 3.20mm, Crimp Contacts, 17 Poles
Comments	Crimp Range 0.14-1.00mm^2
IP Rating	IP67
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906300135

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	150V

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	Straight
Poles	17
Temperature Range - Operating	-40° to +125°C
Wire Size (AWG)	N/A

Obsolete

Downloaded from Arrow.com.

This document was generated on Aug 08, 2026

Obsolete

Downloaded from Arrow.com.