Part Number : 2067640150
Product Description : ISM 868/915MHz Dipole Flexible Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Series Number : 206764
Status : Active
Product Category : Antennas



Documents and Resources

Drawings

2067640150_sd.pdf

2067640100-PK.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

2067640100-AS.pdf

2067640100-PS.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

Downloaded from Arrow.com.

- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Antennas
Series	206764
Description	ISM 868/915MHz Dipole Flexible Antenna, 150.00mm Cable Length, Compatible with U.FL / I-PEX MHF Connectors
Component Type	Flexible Antenna with Cable
Function	Signal
Product Name	ISM 868/915 MHz Stand Alone
Protocol	LoRa, Neul, SigFox, Z-Wave, Zigbee
Type	Internal, ISM Antenna, LPWAN
UPC	191128789172

Electrical

Band#1 F_End (MHz)	870
Band#1 F_Start (MHz)	863
Band#2 F_End (MHz)	928
Band#2 F_Start (MHz)	902
Electrical Connectivity	Cable
Peak Gain (dBi)	1.1 @ 868/915 MHz

Downloaded from Arrow.com.

Return Loss - S11 (dB)	< -9
Total Efficiency	>69% @ 868/915 MHz

Physical

Cable Length	150.00mm
Length	87.40mm
Mounting Style	Adhesive
Net Weight	0.987/g
Packaging Type	PET Film
Polarization	Linear
Radiation Pattern	Omnidirectional
Thickness	0.10mm
Width	12.40mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Jack, Straight, PCB Receptacle, Surface Mount, 1.25mm Mounted Height, 50 Ohms	734120110

Downloaded from Arrow.com.