

1052533-1 Product Details



1052533-1

TE Part Number: 1052533-1
Active
Add to Part List

SMA/QMA RF Connectors

Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Connector
- Jack
- Connector Type = SMA
- Without Snap-Lock
- Terminate To Coaxial Cable

View all Features | Find Similar Products

Live Product Chat

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product
- Request Samples

NEW!

Documentation & Additional Information

Product Drawings:

- OSM 2 HOLE FLANGE MOUNT JACK RECEPTACLE SOLDER POT T... (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

List all Documents

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- Gender = Jack
- Connector Type = SMA
- Body Style = Straight
- Number of Panel Mount Holes = 2
- Body Material = Stainless Steel
- Body Finish = Gold
- Center Contact = With
- Retractable Collar = Without
- Safety Wire Holes = Without
- Dielectric Material = TFE Fluorocarbon

Mechanical Attachment:

- Panel Attachment = With
- Panel Attachment Method = Flange
- Panel Attachment Style = Rear Mount

Electrical Characteristics:

- Impedance (Ω) = 50
- Frequency = DC - 18 GHz
- Insulation Resistance (M Ω) = 10,000

Termination Related Features:

- Coaxial Cable Termination Type = Solder

Body Related Features:

- Snap-Lock = Without
- Length (mm [in]) = 9.53 [0.375]

Contact Related Features:

- Contact Type = Solder Cup
- Center Contact Material = Beryllium Copper
- Center Contact Plating = Gold over Copper

Industry Standards:

- Government/Industry Qualification = No
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C, Reflow solder capable to 245°C, Reflow solder capable to 260°C, Pin-in-Paste capable to 245°C, Pin-in-Paste capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- Terminate To = Coaxial Cable

Other:

- Brand = AMP

Provide Website Feedback | Need Help?