

**Microchip****Filter specification****TFS500C****1/5****Measurement condition**

Ambient temperature:	23	°C
Input power level:	0	dBm
Terminating impedance: *)		
Input:	415 $\Omega$	-1 pF
Output:	415 $\Omega$	-1 pF
External Coil:	33	nH

**Characteristics**

## Remark:

The reference level for the relative attenuation  $a_{rel}$  of the TFS500C is the minimum of the pass band attenuation. This value is defined as the insertion loss  $a_e$ . The nominal frequency  $f_N$  is fixed at 500.0 MHz without any tolerance. The values of relative attenuation  $a_{rel}$  are guaranteed over the whole operating temperature range. The frequency shift of the filter within the operating temperature range is included in the production tolerance scheme.

<b>D a t a</b>		<b>typ. value</b>		<b>tolerance / limit</b>		
<b>Insertion loss</b>	$a_e$	4.0	dB	max.	5.0	dB
(reference level)						
<b>Nominal frequency</b>	$f_N$				500.0	MHz
<b>Passband</b>	PB	390	kHz	$f_N$ ±	0.1	MHz
<b>Passband variation</b>	PBV	1.3	dB	max.	2.0	dB
<b>Relative attenuation</b>	$a_{rel}$					
$f_N$ - 100 MHz ... $f_N$ - 90 MHz		48	dB	min.	40	dB
$f_N$ - 90 MHz ... $f_N$ - 60 MHz		42	dB	min.	38	dB
$f_N$ - 60 MHz ... $f_N$ - 1 MHz		47	dB	min.	40	dB
$f_N$ + 1 MHz ... $f_N$ + 100 MHz		42	dB	min.	40	dB
<b>Input power level</b>		-		max.	15	dBm
<b>Operating temperature range</b>	OTR	-		-40 °C ... +85 °C		
<b>Storage temperature range</b>		-		-55 °C ... +125 °C		
<b>Frequency inversion temperature</b>	$T_0$	18	°C			
<b>Temperature coefficient of frequency</b>	$TC_f$ **)	- 0.036	ppm/K <sup>2</sup>			

\*) The terminating impedances depend on parasitics and q-values of matching elements and the board used, and are to be understood as reference values only. Should there be additional questions do not hesitate to ask for an application note or contact our design team.



\*\*)  $\Delta f = TC_f (T - T_0)^2 f_N$

**Generated:****Checked / Approved:**

**Microchip Frequency Technology GmbH**  
**Potsdamer Straße 18**  
**D 14 513 TELTOW / Germany**  
**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**


Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

## Filter characteristic



## Construction and pin connection


(All dimensions in mm)



1	Input
2	Ground
3	External Coil
4	Ground
5	Output
6	Ground
7	Ground
8	Ground

Date code:	Year + week
N	2021
P	2022
R	2023
...	

## 50 Ω Test circuit



Microchip Frequency Technology GmbH  
 Potsdamer Straße 18  
 D 14 513 TELTOW / Germany  
 Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Stability characteristics, reliability**

After the following tests the filter shall meet the whole specification:

1. Shock: 500 g, 1 ms, half sine wave, 3 shocks each plane;  
DIN IEC 60068 T2 - 27
2. Vibration: 10 Hz to 2000 Hz, 0.35 mm or 5 g respectively, 1 octave per min, 10 cycles per plane, 3 planes; DIN IEC 60068 T2 - 6
3. Change of temperature: -55 °C to 125 °C / 15 min. each / 100 cycles  
DIN IEC 60068 part 2 – 14 Test N
4. Resistance to solder heat (reflow): reflow possible: three times max.;  
for temperature conditions refer to the attached "Air reflow temperature conditions" on page 4;
5. SAW devices are Electrostatic Discharge (ESD) sensitive devices.

This filter is RoHS compliant (2011/65/EU+2015/863/EU)

**Packing**

Tape & Reel: IEC 286 – 3, with exception of value for N and minimum bending radius;  
tape type II, embossed carrier tape with top cover tape on the upper side;


reel of empty components at start: min. 300 mm  
reel of empty components at start including leader: min. 500 mm  
trailer: min. 300 mm

**Tape (all dimensions in mm)**

W	: 12.00 ±0.3
Po	: 4.00 ±0.1
Do	: 1.50 +0.1/-0
E	: 1.75 ±0.1
F	: 5.50 ±0.05
G(min)	: 0.75
P2	: 2.00 ±0.05
P1	: 8.00 ±0.1
D1(min)	: 1.50
Ao	: 4.30 ±0.1
Bo	: 4.30 ±0.1
Ct	: 9.2 ±0.1
Ko	: 1.80 ±0.1
t	: 0.30 ±0.05

**Reel (all dimensions in mm)**

A	: 330 or 180
W1	: 12.4 +2/-0
W2(max)	: 18.40
N(min)	: 50.00
C	: 13.0 +0.5/-0.2



The minimum bending radius is 45 mm.

**Microchip Frequency Technology GmbH**

**Potsdamer Straße 18**


**D 14 513 TELTOW / Germany**

**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Air reflow temperature conditions**

<b>Conditions</b>	<b>Exposure</b>
Average ramp-up rate (30 °C to 217 °C)	less than 3 °C / second
> 100 °C	between 300 and 600 seconds
> 150 °C	between 240 and 500 seconds
> 217 °C	between 30 and 150 seconds
Peak temperature	max. 260 °C
Time within 5 °C of actual peak temperature	between 10 and 30 seconds
Cool-down rate (Peak to 50 °C)	less than 6 °C / second
Time from 30 °C to Peak temperature	no greater than 300 seconds

**Chip-mount air reflow profile****Microchip Frequency Technology GmbH****Potsdamer Straße 18****D 14 513 TELTOW / Germany****Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.

**Microchip****Filter specification****TFS500C****5/5****History**

<b>Version</b>	<b>Reason of Changes</b>	<b>Name</b>	<b>Date</b>
1.0	- Generation of development specification	Bonnen	17.06.2014
2.0	- Change to Filter specification - Change frequency inversion temperature	Bonnen	29.07.2014
2.1	- Change storage temperature range	Bonnen	30.08.2016
2.2	- Change Date code: Year + week	Bonnen	14.09.2016
2.3	- Changed input power level - Updated construction - Updated stability characteristics, reliability	P. Jaster	21.01.2021

**Microchip Frequency Technology GmbH**  
**Potsdamer Straße 18**  
**D 14 513 TELTOW / Germany**  
**Tel: (+49) 3328 4784-0 / Fax: (+49) 3328 4784-30**

Microchip Frequency Technology GmbH reserves the right to make changes to the product(s) and/or information contained herein without notice. No liability is assumed as a result of their use or application. No rights under any patent accompany the sale of any such product(s) or information.