







PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE : 500 V AC (CONT /CONT)

OPERATING TEMPERATURE : -55°C TO 125°C

CONTACT RESISTANCE 20 mΩ MAX

INSERTION FORCE : 0.75N MAX/CONT

EXTRACTION FORCE : 0.15N MIN/CONT

INSULATION RESISTANCE : 10^4 MΩ MIN

NOTES 1. LEAD FREE INDICATOR (LF=LEAD FREE)
PERFORMANCE LEVEL INDICATOR
(REF. DWG. NO. NSC 201844.003)

2. THIS PRODUCT IS CSA APPROVED.
THIS PRODUCT IS UL RECOGNIZED

3. FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING :
BS.A.201572.001

4. THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008

rev	ecn no	dr	date
A	CONVERSION REVISION 06	KN	14-09-01
B	105-0093	MINI	11-06-05
C	DG07-0362	Kason	05-09-07
D	DG10-0110	NZ	08-09-10

		www.fciconnect.com				tolerance 1DEC ± 0.2 1DEC 2DEC ± 0.1 2DEC ANGLES $\pm 1^\circ$ HOEKEN		projection 			
Dr	W.Panis	30-04-96	Product family		MILLIPICS		size	A4		Scale 3/1	
Eng			Spec ref								
Chr			Material				ECN				
Appr											
title MPACS 8+2R RA RCP CONN TYPE E/ SHIELDED						dwg no BS,C ,202260,002		Rev D			
catalog no			HM2R88PA8101----			CUMSTOMER			sheet 1 of 1		