






PERFORMANCE CHARACTERISTICS

CURRENT RATING 1.5 A AT 20°C (FULLY LOADED)
1 A AT 70°C (FULLY LOADED)

RATED VOLTAGE 500V AC (CONT / CONT)

OPERATING TEMPERATURE -55°C TO 125°C

CONTACT RESISTANCE 20 MΩ MAX

INSERTION FORCE :0.75 N MAX /CONT


EXTRACTION FORCE: 0.15 N MIN /CONT

INSULATION RESISTANCE :10⁴ MΩ MIN

NOTES

- LEAD FREE INDICATOR : LF- LEAD FREE
- PERFORMANCE LEVEL INDICATOR
(REF DWG No. BS,C,201844,003)
- THIS PRODUCT IS CSA APPROVED
THIS PRODUCT IS UL RECOGNISED
- FOR RECOMMENDED PTH DIMENSIONS REFER DRAWING: BSA,201,572001
THIS PRODUCT (LF) MEETS EUROPEAN UNION DIRECTIVE
AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.

LAY OUT
P.C.B.-HOLE



Material				Spec ref			
Mat code				tolerance			
Heat treat				projection			
Plating/Finish				MM			
rev	ecn no	dr	date	Dr	4 2 92	J V B	
A	CONV-0001	KN	14-9-91	Eng			
B	105-0093	MINI	08/06/05	Chr			
C	BGM-0356	Gus.M	03/08/05	Appr			
D	BGM-0297	Keson	07/19/06				
E	BGM-0362	Keson	05/09/07				
F	BGM-0010	NZ	2009.30				
Product Family				size			
Model Name				Scale			
Model Revision				REL Level			
MPACS 5+2R RA RCP				BS,C,201418,028			
CONN TYPE A				F			
Pro/E File				sheet 1 of 1			
catalog no							
HMER01PAS10F----							

PDM: Rev 2 F

STATUS: Released

Printed: Mar 15, 2011

These drawings are the property of FCI. They are not to be reproduced, stored in a retrieval system, or transmitted in any form or by any means, electronic, mechanical, photocopying, recording, or by any information storage and retrieval system, without the prior written permission of FCI. Copyright 1992.

FCI

FCI