

COAXIAL ADAPTER, MMPX - SK, 50 Ohm, plug / jack (male / female)

33_MMPX-SK-50-1/199_N

Properties

- Precision interfaces
- Excellent electrical performance
- Premium base materials and platings



Product configuration		
Interface type	Gender	Standard
MMPX	plug (male)	HUBER+SUHNER MMPX STD (Patent US 7.294.023)
SK	jack (female)	MIL-STD-348A/323

Interface and material data		
MMPX		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PPE (Polyphenylene ether, PPO)	
SK		
Piece parts	Material	Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer conductor	Stainless steel	
Body	Stainless steel	
Insulator	PPE (Polyphenylene ether, PPO)	

Electrical data	
Impedance	50 Ω
Interface frequency	40 GHz

Electrical Data (frequency related)		
Frequency range	Return loss	VSWR
0 GHz ... 15 GHz	26 dB	1.105
15 GHz ... 30 GHz	23 dB	1.152

COAXIAL ADAPTER, MMPX - SK, 50 Ohm, plug / jack (male / female)

33_MMPX-SK-50-1/199_N

Electrical Data (frequency related)			
Frequency range	Return loss	VSWR	
30 GHz ... 40 GHz	20 dB	1.222	
Mechanical data			
Weight	0.0022 kg		
Mating cycles	100		
Environmental data			
Operation temperature	-55 °C ... 125 °C		
Material compliance			
Item number	Directive / Regulation	Rating	Exemptions / Details
84071648	RoHS 2011/65/EU and (EU) 2015/863	Compliant with exemption	6c
	REACH 1907/2006 Article 33 SVHC	Contains one or more SVHC >0,1%	CAS: 7439-92-1 Lead
Ordering Information Table			
Item number	Item description		Packaging type
84071648	33_MMPX-SK-50-1/199_NE		Single

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/ EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P2220 / Date of publication: 12.07.2025 / uncontrolled copy