






Technical data

- 1.Nominal voltage: 300V/14A
PITCH:5.0mm
- 2.Connection capacity:
AWG 22-14
- 3.Insulation Withstanding Voltage:
AC 1600V/MIN
- 4.Insulation Resistance:
1000MΩ or more at DC500V
- 5.Tightening torque:
4.0kgf.cm (0.4N.m)
- 6.Screw thread: M2.6
- 7.Stripping length: 5-6mm
- 8.Operating temperature range:-40°C ~ 115°C
- 9.Undimensioned Tolerances:

Dim.L=Px5.0 Dim.B=(P-1)x5.0 P= number of poles(2-24p)		
0-30mm	±0.15	±0.20
over 30mm-60mm	±0.20	±0.25
over 60mm-90mm	±0.25	±0.30
over 90mm	±0.30	±0.40

10.Safety approval:

11.RoHS Compliance

Part No:

OSTTHXX0101

No. of Poles	COLOR
02 2 Poles	0: Black (Standard)
03 3 Poles	2: Red
...	3: Orange
24 24 Poles	4: Yellow
	5: Green
	6: Blue
	8: Grey

Nonstandard colors
Mins could apply

4	WIRE GUARD	PhBz t=0.20mm		P
3	SCREW	STEEL	M2.6x0.4, Zn Plated	P
2	CAGE	BRASS	M2.6x0.4, Tin PLATED	P
1	BODY	PA66 UL94V-0	Black	1
ITEM	NAME OF PART	MATERIAL	NOTES	Q"TY
DWG	WF. Zhang	DATE 2017.08.11	UNITS: MM	SHEET: 1 OF 1
CHK.	WF. Zhang	DATE 2017.08.11	SCALE: NONE 2.5:1 (:)	REV: A
APP.		DATE	TITLE: OSTTH 5.0 Series Solid block "-" slot type 2-24p	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
			PART NO. OSTTHXX0101	
			DWG NO. OSTTHXX0101.dwg	

SIGN	DESCRIPTION	CHK.	DATE



ON-SHORE TECHNOLOGY, INC.

