




REVISION HISTORY			
REV	DESCRIPTION	DATE	APPROVED
B	DCN 41869	11/15	DAL
C	REV. DCN 53565	12/27/23	STW



BODY: PASSIVATED PER AMS 2700.

CENTER CONTACT: GOLD PER ASTM B488, TYPE II, CODE C, CLASS 1.27
OVER NICKEL PER AMS-QQ-N-290, CLASS 1, .000050" MIN.

BAYONET: NICKEL PER AMS-QQ-N-290, CLASS 1, GRADE G.



IMPEDANCE: 50 OHMS
FREQ. RANGE: DC TO 4.0 GHz.
VSWR: 1.30:1 MAX. DC TO 4.0 GHz.

MATERIAL:	SEE NOTES		DIMENSIONS ARE IN INCHES TOLERANCES:		UNLESS OTHERWISE SPECIFIED		 2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES		FRACTIONAL: $\pm 1/64$ ANGULAR: $X^\circ \pm 1^\circ 0'$ $X^\circ X' \pm 15'$		1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA. 'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS		TITLE:	
SURFACE AREA:	N/A		DECIMAL: .X $\pm .030$ $.XX \pm .010$ $.XXX \pm .005$				TITLE: SMA JACK TO BNC PLUG STRAIGHT ADAPTER	
PROPRIETARY THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.	INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994		THIRD ANGLE PROJECTION		DRAWN:		SIZE	
					JRG 01/16/98		DWG. NO.	
					CHECKED:		M55339/44-30001	
					APPROVED:		SCALE: 4:1	
					STW 01/19/98		SHEET 1 OF 1	