






LOCATE HOLES
 $\phi 0.13[.005]$
POSITION DIMENSIONS
ARE BASIC



RECOMMENDED PANEL CUTOUT

MATERIALS:

RJ:

HOUSING & COVER: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES
SEE AMPHENOL PART NUMBER FOR DETAIL.

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

GOLD FLASH ON CONTACT TAILS.

SHIELD: BRASS PLATED WITH NICKEL.

USB:

HOUSING: ENGINEERING THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0,
COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE

PLATING: SELECTIVE GOLD FLASH ON MATING SURFACES

50 μ " [1.27 MICRONS]

MIN. NICKEL UNDERPLATE

100 μ " TIN PLATING ON CONTACT TAILS

SHIELD: BRASS PLATED WITH NICKEL.

AMPHENOL PARTNUMBER: RJE36-188-2X03

GOLD PLATING
0 = GOLD FLASH
1 = 6 μ INCH
2 = 15 μ INCH
3 = 30 μ INCH
4 = 50 μ INCH

UNLESS SPECIFIED OTHERWISE		DRAWN	DATE	Amphenol Canada Corp.	
PRIMARY UNITS	MILLIMETER	HANSON.C	SEP 03/18	Commercial Products	
SECONDARY		CHECKED	AMY.Z	TITLE	
REFERENCE IN PARENTHESES		M.E. APP'D		RJ45 OVER SINGLE USB 2.0 COMBO, DIP TYPE	
		Q.A. APP'D		WITHOUT TABS AND LEDS -RoHS COMPLIANT	
GENERAL TOLERANCES		DWG APPR.	L.CHAN	DWG. NO.	
1 DECIMAL PLACE	± 0.30	ENG. REL. NO.	SEP 03/18	P-RJE36-188-2X03	
2 DECIMAL PLACES	± 0.25	REF.		REV	
3 DECIMAL PLACES	± 0.20	THIRD ANGLE PROJECTION		A	
ANGULAR DEGREES	$\pm 1.0^\circ$	DO NOT SCALE DRAWING		CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	