
**Part Number :** 1300680105
**Product Description :** BradPower D-Size (1 3/8"–M35) 3-Pole Reducing Tee, with 3-Pole BradPower A-Size (7/8"–M22) Drop, Red
**Series Number :** 130068
**Status :** Active
**Product Category :** Industrial Tees and Splitters
**Engineering Part Number :** TC30130-200E



## Documents and Resources

### Drawings

1300680105_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Contains Boron oxide; Methanaminium, N-[4-[[4-(dimethylamino)phenyl][4-(phenylamino)-1-nap..... per D(2022)9120-DC (17 Jan 2023) |
| EU RoHS | Compliant with Exemption 6(c) per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

Downloaded from Arrow.com.

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Industrial Tees and Splitters |
| Series | 130068 |
| Description | BradPower D-Size (1 3/8"–M35) 3-Pole Reducing Tee, with 3-Pole BradPower A-Size (7/8"–M22) Drop, Red |
| IP Rating | IP67 |
| Product Name | BradPower D-Size |
| Type | Power Tap Tee |
| UPC | 78172545165 |

### Agency

| | |
|---|---|
| UL | E258922 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 15.0A, 32.0A |
| Voltage - Maximum | 600V AC/DC |

### Physical

| | |
|---|---|
| Drop Connector | BradPowerA-Size (7/8"–M22) |
| Drop Gender | Female |
| Keyway | Single |

Downloaded from Arrow.com.

| | |
|---|---|
| Left Trunk Connector | BradPower D-Size (1 3/8"–M35) |
| Left Trunk Gender | Female |
| Leg 1 Length | N/A |
| Leg 2 Length | N/A |
| Material - Cable Jacket | N/A |
| Material - Connector Body | PVC |
| Material - Coupling Nut | Anodized Aluminum |
| Net Weight | 252.650/g |
| Poles | 3 |
| Right Trunk Connector | BradPower D-Size (1 3/8"–M35) |
| Right Trunk Gender | Male |
| Temperature Range - Operating | -20° to +90°C |



Downloaded from Arrow.com.