



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-19-002730	02AUG2019	A.S	H.L

D

C

B


A



VIEW M


NOTES:

- ⚠ MATERIAL CONTACT: PHOSPHORBRONZE
MATERIAL HOUSING: GLASSFILLED POLYESTER
UL-RATING 94V0 (GRAY).
- ⚠ GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27μm NICKEL MIN. AND ACTION PIN: 0,5μm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- ⚠ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⚠ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, UNCONTROLLED ENVIRONMENT APPLICATIONS.
- ⚠ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
- ⚠ CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE.
- ⚠ PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID (110 HOLES).
- ⚠ HOLES IN ROW f AND z FOR POSSIBLE FUTURE USE OF
GROUND RETURN SHIELD. (SHIELDS NOT YET TOOLED)
- ⚠ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI





COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT

P.C.B. HOLE DIM. ACTION PIN
FOR DETAILS SEE
APPLICATION SPECIFICATION



SECTION A-A



VIEW M
SCALED

OBSOLETE	11	267	1	1-5352268-9		
		257	1	-5352268-9		
		24	1	-5352268-4		
		23	1	5352268-1		
FINISH			MATERIAL	PARTNUMBER		
UMENT.	DWN K.N.KIRAN	23AUG2004	 TE Connectivity			
CHK B.MOOIJ	27OCT2004	NAME				
APVD B.MOOIJ	27OCT2004					
PRODUCT SPEC						
±0.2	108-19082		Z-PACK 2mm HM TYPE B 110 POS. 22 COLUMNS VERTICAL FEMALE CONNECTOR ASSEMBLY			
	APPLICATION SPEC					
	114-19029					
WEIGHT	0.000000		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
	A2 00779		C-5352268		—	
CUSTOMER DRAWING			SCALE	SHEET		REV
			5:1	1 of 1		F