



Part Number : [1200060022](#)

Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (90°) to Pigtail, 0.34mm² PVC Cable, 5.0m (16.40') Length

Series Number : 120006

Status : Active

Product Category : Circular Industrial Cordsets

Engineering Part Number : 804001E03M050




Documents and Resources

Drawings

[1200060022 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:1574523b-604d-4ede-a993-eb61611adef1
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120006
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, A-Coded, Female (90°) to Pigtail, 0.34mm ² PVC Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	800756927534

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Cable Diameter	5.40mm (.213")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black

Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	244.530/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-30° to +80°C
Wire/Cable Type	UL 2464
Wire Size (AWG)	N/A

This document was generated on May 20, 2026