




PRODUCT NUMBER	PITCH
ETxx02x200J0G	7.62 mm



N = Number of poles
 Dim L = $N \times 7.62$
 Dim P = $(N-1) \times 7.62$
 Dim B = $(N-1) \times 7.62 + 22.86$
 Dim C = $(N+2) \times 7.62$
 Dim D = $(N-1) \times 7.62 + 15.24$

poles	Tolerance
2-4p	± 0.15
5-8p	± 0.20
9-12p	± 0.30
13-16p	± 0.40

PART NO.: ET xx 02 x 2 00J0 G

Solid block		Color	RoHS compliant (lead<4%) In copper Alloy
No. of poles			
02 2 poles	3	Red (RAL3001/D)	
03 3 poles	4	Orange(RAL2011/P)	
...	5	Yellow(RAL1018/A)	
...	6	Green(RAL6018/T)	
16 16 poles	7	Blue (RAL5015/A)	
	8	Grey(RAL7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

Material:

- Item ① Terminal(housing): Thermoplastic (UL94V-0)
- Item ② Terminal(cover): Thermoplastic (UL94V-0)
- Item ③ Clamp: Brass Ni plated
- Item ④ Female contact : Copper. Tin plated
- Item ⑤ Wire guard: Stainless steel
- Item ⑥ Terminal Screw: Steel , zinc plating " * " slot type
- Item ⑦ With flange Screw: Steel Zinc plating M3"+/-" slot type

Electrical:

	cULus	TUV
● Voltage rating:	300V/600V	800V
● Current rating:	32A/41A	32A
● Wire range:		0.2-6mm ²
● Solid wire(AWG):	8-24	
● Stranded wire(AWG):	8-24	
● Torque:	7 LB-In	0.8N.m
● Screw:	M3.5	
● Wire strip length:	10-11 mm	
● Withstanding Voltage:	1.6KV	6KV
● Operating temperature:	-40°C to +115°C	
● Safety Approval:	cULus	TUV

mat'l. code				surface	tolerance	projection	product family	
ltr ecn no dr date				ASME Y14.5	ASME Y14.5		TERMINAL BLOCK	
				tolerances unless otherwise specified		MM	title	
				angles	X.±0.5		TERMINAL BLOCK	
				±	X.X±0.3		PLUGGABLE PLUG, WITH FLANGE	
				X'±1"	X.XX±0.1	scale	dwg no	
				dr	EVIN ZHONG 041814		sheet 1 of 1	
				enrg	EVIN ZHONG 041814		size	
				chr	HANKE FENG 041814		A4	
				appd	SHI JUN 041814		type	
							CUSTOMER Drawing	
sheet index	revision	A	1					