



700 V, 80 mΩ typ., 21.7 A, e-mode PowerGaN transistor



**PowerFLAT 8x8 HV
for PowerGaN**



G8D1234S56TABKS7



Features

Order code	V_{DS}	$R_{DS(on)}$ max.	I_D	Series
SGT105R70ILB	700 V	105 mΩ	21.7 A	G-HEMT

- Enhancement mode normally off transistor
- Very high switching speed
- High power management capability
- Extremely low capacitances
- Kelvin source pad for optimum gate driving
- Zero reverse recovery charge
- ESD safeguard

Applications

- Adapters for tablets, notebook and AIO
- USB type-C PD adapters and quick chargers
- AC-DC converters
- DC-DC converters

Description

The SGT105R70ILB is a 700 V, 21.7 A e-mode PowerGaN transistor combined with a well established packaging technology. The resulting G-HEMT device provides extremely low conduction losses, high current capability and ultra fast switching operation to enable high power density and unbeatable efficiency performances.

Product status link

[SGT105R70ILB](#)

Product summary

Order code	SGT105R70ILB
Marking	105R70I
Package	PowerFLAT 8x8 HV for PowerGaN
Packing	Tape and reel

1 Electrical ratings

$T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise specified.

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	700 ⁽¹⁾	V
	Drain-source voltage (transient, $t_p < 200\text{ }\mu\text{s}$)	800	
V_{GS}	Gate-source voltage	-6 to 7	V
I_D	Drain current (continuous) at $T_C = 25\text{ }^{\circ}\text{C}$	21.7 ⁽²⁾	A
I_{DM}	Pulse drain current ($t_p = 10\text{ }\mu\text{s}$)	43.5	A
P_{TOT}	Total power dissipation at $T_C = 25\text{ }^{\circ}\text{C}$	158	W
ESD	Human body model, $R = 1.5\text{ k}\Omega$, $C = 100\text{ pF}$	2	kV
T_{stg}	Storage temperature range	-55 to 150	$^{\circ}\text{C}$
T_J	Operating junction temperature range		$^{\circ}\text{C}$

1. Recommended continuous maximum bus voltage during switching operations should not exceed 450 V.
2. Limited by design.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case	0.79	$^{\circ}\text{C/W}$
R_{thJA}	Thermal resistance, junction-to-ambient	65 ⁽¹⁾	$^{\circ}\text{C/W}$

1. When mounted on a standard 1 inch² area of FR-4 PCB with 2-oz copper.

2 Electrical characteristics

$T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise specified.

Table 3. Static

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{DSS}	Drain-source leakage current	$V_{GS} = 0\text{ V}, V_{DS} = 700\text{ V}$		3.8	48.8	μA
		$V_{GS} = 0\text{ V}, V_{DS} = 700\text{ V}, T_J = 150\text{ }^{\circ}\text{C}$		9.8		
I_{GSS}	Gate-source leakage current	$V_{DS} = 0\text{ V}, V_{GS} = 6\text{ V}$		122.3		μA
$V_{GS(th)}$	Gate threshold voltage	$V_{DS} = V_{GS}, I_D = 24.3\text{ mA}$	1.2	1.7	2.5	V
$R_{DS(on)}$	Static drain-source on-resistance	$V_{GS} = 6\text{ V}, I_D = 6\text{ A}$		80	105	$\text{m}\Omega$
		$V_{GS} = 6\text{ V}, I_D = 6\text{ A}, T_J = 150\text{ }^{\circ}\text{C}$		180		

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	$V_{GS} = 0\text{ V}, V_{DS} = 400\text{ V}, f = 100\text{ kHz}$	-	179	-	pF
C_{oss}	Output capacitance		-	66.2	-	pF
C_{rss}	Reverse transfer capacitance		-	0.7	-	pF
$C_{o(er)}^{(1)}$	Equivalent output capacitance energy related	$V_{GS} = 0\text{ V}, V_{DS} = 0\text{ to }400\text{ V}$	-	102	-	pF
$C_{o(tr)}^{(2)}$	Equivalent output capacitance time related		-	140	-	pF
R_g	Intrinsic gate resistance	$f = 5\text{ MHz}, I_D = 0\text{ A}$	-	2.3	-	Ω
V_{plat}	Gate plateau voltage	$V_{DS} = 400\text{ V}, I_D = 6\text{ A}$	-	2.2	-	V
Q_g	Total gate charge	$V_{GS} = 0\text{ to }6\text{ V}, V_{DS} = 400\text{ V}, I_D = 6\text{ A}$	-	4.8	-	nC
Q_{gs}	Gate-source charge		-	0.4	-	nC
Q_{gd}	Gate-drain charge		-	2.2	-	nC
Q_{rr}	Reverse recovery charge	$V_{GS} = 0\text{ V}, V_{DS} = 400\text{ V}$	-	0	-	nC
Q_{oss}	Output charge		-	56	-	nC

- $C_{o(er)}$ is a constant capacitance value that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to the stated value.
- $C_{o(tr)}$ is a constant capacitance value that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to the stated value.

Table 5. Reverse conduction

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_{SD}	Source-drain reverse voltage	$V_{GS} = 0\text{ V}, I_{SD} = 6\text{ A}$	-	2.6	-	V

2.1 Electrical characteristics (curves)







Figure 1. Safe operating area ($T_C = 25^\circ\text{C}$)

Figure 2. Safe operating area ($T_C = 125^\circ\text{C}$)

Figure 3. Maximum transient thermal impedance

Figure 4. Total power dissipation

Figure 5. Typical output characteristics ($T_J = 25^\circ\text{C}$)

Figure 6. Typical output characteristics ($T_J = 125^\circ\text{C}$)








Figure 7. Typical transfer characteristics

Figure 8. Normalized on-resistance vs temperature

Figure 9. Typical drain-source on-resistance ($T_J = 25 \text{ }^{\circ}\text{C}$)

Figure 10. Typical drain-source on-resistance ($T_J = 125 \text{ }^{\circ}\text{C}$)

Figure 11. Typical gate charge characteristics

Figure 12. Typical capacitance characteristics









Figure 13. Typical output capacitance charge

Figure 14. Typical output capacitance stored energy

Figure 15. Typical diode reverse conduction characteristics ($T_J = 25^\circ\text{C}$)

Figure 16. Typical diode reverse conduction characteristics ($T_J = 125^\circ\text{C}$)

Figure 17. Typical reverse conduction characteristics ($T_J = 25^\circ\text{C}$)

Figure 18. Typical reverse conduction characteristics ($T_J = 125^\circ\text{C}$)


Figure 19. Normalized gate threshold vs temperature



3 Test circuits

Figure 20. Test circuit for inductive load switching times





Figure 21. Switching time waveforms




AM01473v1

4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 PowerFLAT 8x8 HV for PowerGaN package information

Figure 22. PowerFLAT 8x8 HV for PowerGaN package outline




DM001104683_rev.2_PowerGaN


Table 6. PowerFLAT 8x8 HV for PowerGaN mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	0.80	0.85	0.90
A1	0.00	0.02	0.05
b	0.95	1.00	1.05
b1	0.25 REF		
b2	0.20 REF		
b3	0.35	0.40	0.45
c	0.203 REF		
D	7.90	8.00	8.10
D2	6.84	6.94	7.04
Nd	6.00 BSC		
e	2.00 BSC		
e1	0.30 BSC		
e2	0.90 BSC		
E	7.90	8.00	8.10
E2	3.10	3.20	3.30
L	0.45	0.50	0.55
L1	0.20 REF		
L2	0.10 REF		
K	2.80 REF		
K1	1.00 REF		
K2	0.40 REF		
R	0.20 REF		

Figure 23. PowerFLAT 8x8 HV for PowerGaN recommended footprint (dimensions are in mm)



DM001104683_rev.2_PowerGaN_footprint

Figure 24. Marking composition for PowerFLAT 8x8 HV for PowerGaN


DM01133839_rev.1

Engineering samples


These samples are clearly identified by "ES" digits in the marking additional information field of each unit. These samples are intended to be used for electrical compatibility evaluation only; usage for any other purpose may be agreed only upon written authorization by ST. ST is not liable for any customer usage in production and/or in reliability qualification trials.

Commercial samples

Fully qualified parts from ST standard production with no limitations of use or special identification marking.


4.2 PowerFLAT 8x8 HV packing information

Figure 25. PowerFLAT 8x8 HV tape (dimensions are in mm)



8229819_2_0

Figure 26. PowerFLAT 8x8 HV package orientation in carrier tape



Revision history

Table 7. Document revision history

Date	Revision	Changes
21-May-2025	1	First release.
29-May-2025	2	Updated <i>Figure 5. Typical output characteristics</i> ($T_J = 25\text{ °C}$).
15-May-2026	3	Updated Section 4.2: PowerFLAT 8x8 HV packing information.

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice.

In the event of any conflict between the provisions of this document and the provisions of any contractual arrangement in force between the purchasers and ST, the provisions of such contractual arrangement shall prevail.

The purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

The purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of the purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

If the purchasers identify an ST product that meets their functional and performance requirements but that is not designated for the purchasers' market segment, the purchasers shall contact ST for more information.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2026 STMicroelectronics – All rights reserved