



+ RELAYS, CONTACTORS & SWITCHES

FULL-SIZE RELAYS



✓ Active

TE CONNECTIVITY (TE)
B07B055AC1 = 07 RELAY
CII

B07B055AC1
TE Internal Number: 5-1617002-0

Not EU RoHS Compliant
Not EU ELV Compliant

Contact Arrangement 2 Form C, DPDT, 2 C/O
Input Voltage (VDC) 26.5
Contact Current Rating (A) 10
Coil Voltage (VDC) 26.5
Coil Resistance (Ω) 300

↓ 3D PDF

DOCUMENTATION

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Customer View Model
3D_IGS.ZIP
English

Customer View Model
3D_STP.ZIP
English

Catalog Pages/Data Sheets

RELAY

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

- Enclosure Type** Hermetically Sealed
- Relay Type** Military/Aerospace High Performance
- Product Type** Relay
- Coil Latching** Without
- MOSFET Driver** Without

Configuration Features

- Transistor Driver** Without

Electrical Characteristics

- Input Voltage (VDC)** 26.5
- Coil Voltage (VDC)** 26.5
- Coil Resistance (Ω)** 300
- Coil Power Rating (DC) (mW)** 2341
- Coil Power Measurement** Milliwatts
- Vibration** 20G's, 10 – 2000Hz
- Coil Magnetic System** Non-Polarized, Monostable
- Shock** 50G's, 11ms
- Coil Suppression Diode** With
- Coil Polarity Protection Diode** Without
- Actuating System** DC

Contact Features

- Contact Arrangement** 2 Form C, DPDT, 2 C/O
- Contact Current Rating (A)** 10

Termination Features

- Termination Type** PC Pins

Mechanical Attachment

- Mounting Type** Printed Circuit Board

Usage Conditions

- Operating Temperature Range (°C)** -55 – 85

Statement of Compliance

Statement of Compliance

