


COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)
11_BNC-50-2-1/133_N

Properties

- Useful for frequently coupled and uncoupled connections
- Available for 50 ohm and 75 ohm applications
- Applicable in frequencies up to 4 GHz



Product configuration		
Interface type	Gender	Standard
BNC	plug	IEC 60169-8_MIL-STD-348A/301_CECC 22120

Interface and material data		
Piece parts	Material	Plating
Centre contact	Brass	Gold Plating (Nickel underplated)
Outer conductor	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	

Electrical data	
Impedance	50 Ω
Interface frequency	4 GHz

Mechanical data	
Weight	0.0173 kg
Mating cycles	500
Cable entry centre contact	soldered
Cable entry outer contact	clamped

Environmental data	
Operation temperature	-65 °C ... 165°C

COAXIAL CONNECTOR, BNC, 50 Ohm, Straight cable plug (male)
11_BNC-50-2-1/133_N

Ordering Information Table		
Item number	Item description	Packaging type
22540029	11_BNC-50-2-1/133_NE	Single

Suitable cables	
Cable group	X3 - 2 mm / 50 Ohm U2 - 2 mm / 50 Ohm
Suitable cables	RG_316_/U RG_188_A/U
Additional cables	RG_174_/U

Additional Information	
Only as assembly	No

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT PIM-P3707 / Date of publication: 25.11.2023 / uncontrolled copy