

## OmniVS 120V 800VA 475W Line-Interactive UPS, Tower, USB port, TAA

MODEL NUMBER: **OMNIVS800**



### Highlights

- 800VA tower 120V line interactive UPS
- Corrects brownouts as low as 89V without using battery power
- 6 UPS battery supported outlets, 1 surge-only outlet
- USB port, TEL/DSL/ethernet protection
- NEMA 5-15P input plug and 7 NEMA 5-15R outlets

### Package Includes

- OMNIVS800 Line Interactive UPS
- USB and telephone cable
- User manual with warranty information

### Description

OMNIVS800 line-interactive UPS system offers voltage regulation, surge suppression and long-lasting battery support for personal computers, internetworking equipment and other sensitive electronics. Internal UPS circuits support entry-level PC systems for up to 60 minutes during power failures so that connected equipment can be shut down without data loss. Automatic Voltage Regulation (AVR) circuits regulate brownouts as low as 89 volts back to usable levels without using battery power. Offers complete desktop power protection in an attractive black tower configuration. Includes six battery-supported outlets for computer, monitor and one vital system peripheral, plus one additional surge suppression-only outlet for printers and other system accessories not requiring battery support. HID-compliant USB port enables optional unattended system shutdown without data loss in case of extended power failure; USB cable included. HID-compliant USB port also enables direct integration with built-in power management and auto-shutdown features of Windows and macOS. PowerAlert® software available via free download. Built-in single-line phone/Ethernet suppression jacks protect modem, fax machine, cordless phone or other peripheral with a standard dialup, DSL or data line connection. Built-in audible alarm and four front-panel LEDs indicate line power status, battery power status, battery low/replace status and voltage boost operation. 800VA/475W power handling ability supports entry-level PCs, network workstations, point-of-sale equipment, small business phone systems, audio/video equipment and home theater systems. Offers 3.5 minutes battery runtime with a full load of 800VA and 11.5 minutes with a half load of 400VA. Supports battery replacement via built-in access panel.

### Features

- OMNIVS800 Uninterruptible Power Supply offers voltage regulation, surge suppression and long lasting battery support
- Supports entry-level PCs up to 60 minutes during blackouts to enable shutdown without data loss
- Regulates brownouts as low as 89 volts back to usable levels without using battery power
- 6 UPS battery supported/surge protected outlets, plus 1 additional surge suppression-only outlet
- USB port enables data-saving unattended shutdown when used with PowerAlert software, available via FREE download from [tripplite.eaton.com/products/power-alert](http://tripplite.eaton.com/products/power-alert)
- HID-compliant USB port also enables direct integration with built-in power management and auto-shutdown features of Windows and macOS
- Single line phone/Ethernet suppression jacks protects standard dialup/DSL, or Ethernet connections
- Audible alarm and 4 front panel LEDs offer complete UPS and line power status information
- 800VA/475 watt power handling ability supports a variety of sensitive electronic equipment
- 3.5 minutes full load runtime (800VA), 11.5 minutes half load runtime (400VA)



Powering Business Worldwide

TRIPP LITE  
SERIES

- Supports battery replacement via built-in access panel
- Optional PDUB15 bypass PDU enables hot-swappable UPS replacement with no disruption to connected equipment
- \$200,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Specifications

OVERVIEW	
UPC Code	037332120953
UPS Type	Line-Interactive
INPUT	
Input Phase	Single-Phase
Rated input current (Maximum Load)	12A
Nominal Input Voltage(s) Supported	120V AC
UPS Input Connection Type	5-15P
UPS Input Cord Length (ft.)	6
UPS Input Cord Length (m)	1.8
Recommended Electrical Service	15A 120V
Maximum Input Amps	12
OUTPUT	
Output Capacity (VA)	800
Output Capacity (kVA)	0.8
Output Capacity (Watts)	475
Output Capacity (kW)	0.475
Nominal Voltage Details	115v nominal output in battery mode
Frequency Compatibility	60 Hz
Output Voltage Regulation (Battery Mode)	+/- 5%
UPS Output Receptacles (Surge Suppression Only)	6 UPS outlets, 1 surge-only outlet
Hot-Swap PDU options	PDUB15 (2U / 8 5-15R outlets)
Output AC Waveform (AC Mode)	Sine wave
Output AC Waveform (Battery Mode)	PWM sine wave
Nominal Output Voltage(s) Supported	110V; 115V; 120V
Output Receptacles	(7) 5-15R
Individually Controllable Load Banks	No

BATTERY	
Battery Type	Valve Regulated Lead Acid (VRLA)
Runtime Full Load (min.)	3.5 min. (475W)
Runtime Half Load (min.)	11.5 min. (238W)
Expandable Runtime	No
DC System Voltage (VDC)	12
Battery Recharge Rate (Included Batteries)	Less than 4.5 hours from 10% to 90%
Battery Access	Battery access door
Internal UPS Replacement Battery Cartridge	<a href="https://tripplite.eaton.com/UPS-Replacement-Battery-Cartridge-Tripp-Lite-APC-Belkin-Best-Powerware-Liebert-other-UPS-RBC51">RBC51</a>
Battery Replacement Description	Hot-swappable, user replaceable batteries
VOLTAGE REGULATION	
Voltage Regulation Description	Automatic voltage regulation (AVR) maintains line power operation with input voltage as low as 89
Undervoltage Correction	Input voltages between 89 and 105 are boosted by 14%
USER INTERFACE, ALERTS & CONTROLS	
Switches	2 Switches control off/on power status and alarm-cancel/self-test operation
Alarm Cancel Operation	Power-fail alarm can be silenced using alarm-cancel switch; once silenced, alarm will re-sound to indicate low-battery status
Audible Alarm	Audible alarm indicates power-failure and low-battery conditions
LED Indicators	4 LEDs indicate line power, battery power, overload and battery low/replace status
SURGE / NOISE SUPPRESSION	
UPS DataLine Suppression	1 line TEL/DSL (1 in / 1 out); 10/100Base T Ethernet
EMI / RFI AC Noise Suppression	Yes
AC Suppression Joule Rating	510
AC Suppression Response Time	Instantaneous
PHYSICAL	
Primary Form Factor	Tower
Rack Height	0U
Installation Form Factors Supported with Included Accessories	Tower
Installation Form Factors Supported with Optional Accessories	Wallmount ( <a href="https://tripplite.eaton.com/Wall-Mount-Bracket-Installation-Accessories-for-UPS-Systems-UPSWM">UPSWM</a> ); - tower mounting kit)
Primary UPS Depth (mm)	191
Primary UPS Height (mm)	274
Primary UPS Width (mm)	132



Powering Business Worldwide

TRIPP LITE  
SERIES

Shipping Dimensions (hwd / in.)	8.70 x 13.90 x 7.70
Shipping Dimensions (hwd / cm)	22.10 x 35.31 x 19.56
Shipping Weight (lbs.)	17.50
Shipping Weight (kg)	7.94
UPS Housing Material	PVC
UPS Power Module Dimensions (hwd, cm)	27.43 x 13.21 x 19.05
UPS Power Module Dimensions (hwd, in.)	10.8 x 5.2 x 7.5
UPS Power Module Weight (kg)	7.21
UPS Power Module Weight (lbs.)	15.9
Unit Dimensions (hwd / in.)	10.750 x 5.250 x 7.500
Unit Weight (lbs.)	15.2500
Unit Weight (kg)	6.92
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	5° to 122°F (-15° to 50°C)
Relative Humidity	0-95% non-condensing
AC Mode BTU / Hr. (Full Load)	24
AC Mode Efficiency Rating (100% Load)	97%
Battery Mode Heat Dissipation (BTU/Hr) @ Full Load	631
<b>COMMUNICATIONS</b>	
PowerAlert Software	For local monitoring via the UPS's built-in USB ports, download PowerAlert software at <a href="https://tripplite.eaton.com/products/power-alert">https://tripplite.eaton.com/products/power-alert</a>
Communications Cable	USB interface cable included
WatchDog Compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
Network UPS Tools (NUT) Compatibility	NUT compatible. See a full list of NUT compatible Tripp Lite UPS systems at <a href="https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite">https://networkupstools.org/stable-hcl.html?manufacturer=Tripp%20Lite</a>
Network Management Card Description	Network management not supported
Communications Interface	USB (HID enabled)
<b>LINE / BATTERY TRANSFER</b>	
Transfer Time	2-4 milliseconds
Low Voltage Transfer to Battery Power (Setpoint)	89
High Voltage Transfer to Battery Power (Setpoint)	139



Powering Business Worldwide

TRIPP LITE  
SERIES

FEATURES & SPECIFICATIONS	
Cold Start (Startup in Battery Mode During a Power Failure)	Cold-start operation supported
High Availability UPS Features	Automatic Voltage Regulation (AVR); Hot swappable batteries; Surge/noise protection
Green Energy-Saving Features	Greater than 95% efficiency - GREEN UPS
APPLICATIONS	
UPS Applications	Home/Office Desktop; Retail/Point of Sale; Hospitality
STANDARDS & COMPLIANCE	
Product Certifications	CSA (Canada); NOM (Mexico); UL 1778
Product Compliance	ENERGY STAR Qualified
WARRANTY & SUPPORT	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (Latin America)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$200,000&nbsp;<a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime Insurance</a>&nbsp;

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2026 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.