


DATA CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO EMERSON CONNECTIVITY SOLUTIONS AND SHALL NOT BE DISCLOSED, COPIED OR USED FOR PROCUMENT OR MANUFACTURE WITHOUT EXPRESS WRITTEN PERMISSION

REVISIONS


REV	DESCRIPTIONS	DATE	APPROVED
P	REVISED PER ECO 16924	6/4/09	







SCALE 2/1



RECOMMENDED PANEL CUTOUT

4. SUBMINIATURE TRIAXIAL SOLDER POT BULKHEAD MOUNT 3-LUG RECEPTACLE (TPS STYLE)

3 SOLDER POT ACCEPTS Ø.034 MAXIMUM CONDUCTOR

2. MAXIMUM PANEL THICKNESS: .187

1 FINISH: TFS-1A (NICKEL)

NOTES: UNLESS OTHERWISE SPECIFIED.

N/A	
BLANK LENGTH (REF. ONLY)	
N/A	
SURFACE AREA	

INTERPRET DRAWING PER MIL-STD-100. DIMENSIONS ARE IN INCHES AND INCLUDE FINISH THICKNESS UNLESS OTHERWISE SPECIFIED.

TOL: UNLESS SPECIFIED.
.XX ± .02
.XXX ± .010
ANGLE ± 1°

DRN	M JOHNSON	5/8/09
CHK	LM	5/25/09
QUALITY		
MANUF		
APPROVED	LM	5/25/09
PRO/E FILE NO.	3-0027	

MATERIAL:

FINISH: 1

DO NOT SCALE DWG

cinch CONNECTIVITY SOLUTIONS a bel group

Cinch Connectivity Solutions
299 Johnson Ave. Ste. 100
Waseca, MN 56093
1-800-247-8256

TITLE: BJ157

SIZE	CAGE CODE	DRAWING NO.	REV.
A	14949	3-0027	P

SCALE	DATE	SHEET
1/1	12-22-75	1 OF 2

Downloaded from Arrow.com.
Please read our datasheet & drawing disclaimer here.