

Fuse plug - ST-SILED 60-UK 4 - 0921040

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Fuse plug, nominal current: 6.3 A, length: 33.1 mm, width: 6.1 mm, height: 45.7 mm, color: black

The figure shows the version without LED/light indicator

RoHS

Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4017918010300
Weight per Piece (excluding packing)	5.800 g
Custom tariff number	85369095
Country of origin	Poland

Technical data

General

Note	If the fuse is defective, the downstream circuit is not off load
Color	black
Insulating material	PA
Flammability rating according to UL 94	V2

Dimensions

Width	6.1 mm
Length	33.1 mm
Height	45.7 mm

General

Fuse plug - ST-SILED 60-UK 4 - 0921040

Technical data

General

Insulating material group	CTI 600
LED voltage range	30 V AC/DC ... 60 V AC/DC
Nominal current I_N	6.3 A
Nominal voltage U_N	60 V
Fuse	G / 5 x 20
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	125 °C
Static insulating material application in cold	-60 °C
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed
Calorimetric heat release NFPA 130 (ASTM E 1354)	27,5 MJ/kg
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3

Connection data

Connection method	Plug-in connection
-------------------	--------------------

Ambient conditions

Operating temperature	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Permissible humidity (storage/transport)	30 % ... 70 %
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Classifications

eCl@ss

eCl@ss 10.0.1	27142001
eCl@ss 11.0	27141149
eCl@ss 4.0	27142000
eCl@ss 4.1	27142000
eCl@ss 5.0	27142000

Fuse plug - ST-SILED 60-UK 4 - 0921040

Classifications

eCl@ss

eCl@ss 5.1	27141100
eCl@ss 6.0	27142000
eCl@ss 7.0	27142001
eCl@ss 9.0	27142001

ETIM

ETIM 2.0	EC000897
ETIM 3.0	EC000897
ETIM 4.0	EC002018
ETIM 6.0	EC000035
ETIM 7.0	EC002018

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121409
UNSPSC 11	39121409
UNSPSC 12.01	39121409
UNSPSC 13.2	39121629
UNSPSC 18.0	39121629
UNSPSC 19.0	39121629
UNSPSC 20.0	39121629
UNSPSC 21.0	39121629

Approvals

Approvals

Approvals

EAC / cULus Recognized

Ex Approvals

Approval details

EAC		RU C- DE.BL08.B.00714
-----	---	--------------------------

Fuse plug - ST-SILED 60-UK 4 - 0921040

Approvals

cULus Recognized			http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425
Nominal voltage UN		24 V		
Nominal current IN		10 A		

Phoenix Contact 2021 © - all rights reserved
<http://www.phoenixcontact.com>