




Part Number : [2005062019](#)

Product Description : stAK50h 2 Bay Right-Angle Hybrid Header, 50 Circuits, Bay 1: 25 Circuits/Key 1/ Green; Bay 2: 25 Circuits/Key 2/Gray; Tube

Series Number : 200506

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2005062019_sd.pdf](#)

[2005028100-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2005060000-AS-000.pdf](#)

[2005060000-AS-CH-000.pdf](#)

[2005060001-PS-000.pdf](#)

[2005060001-PS-CH-000.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

[Compliance Statements](#)

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	200506
Description	stAK50h 2 Bay Right-Angle Hybrid Header, 50 Circuits, Bay 1: 25 Circuits/Key 1/Green; Bay 2: 25 Circuits/Key 2/Gray; Tube
Application	Automotive, Wire-to-Board
Component Type	PCB Header
Product Name	stAK50h
UPC	195842801011

Electrical

Current - Maximum per Contact	5.0A, 30.0A
Voltage - Maximum	14V DC

Physical

Breakaway	No
Circuits (Loaded)	50
Circuits (maximum)	50
Color - Resin	Green, Gray

Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	SPS
Net Weight	21.694/g
Number of Rows	5
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm, 7.20mm
Pitch - Termination Interface	2.00mm, 4.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	Yes
Temperature Range - Operating	-40° to +105°C LV-214, -40° to +85°C GMW3191 June2012
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
stAK50h Hybrid Receptacle, 25 Circuits, Key 1, Rib Option A, Light Green, Bag	<u>1600270011</u>
stAK50h Hybrid Receptacle, 25 Circuits, Key 2, Rib Option A,	<u>1600270012</u>

Stone Gray, Bag	
-----------------	--

This document was generated on May 26, 2026