Product data sheet

Specifications



APC NetShelter 13U Wallmount Rack Cabinet Glass Door Double Hinged Server Depth

AR100

Overview

Presentation

Ideal for retail, healthcare, and educational facilities, the wall rack offers an efficient solution for deploying server and networking equipment for edge computing applications. For areas with limited floor space. Designed to house your server, as well as network solutions such as network switches and patch panels. Rack hinges at the rear allowing for access to the back of the rack during installation and setup or while undergoing maintenance. The door is reversible allowing for the door to open direction desired to avoid interference with its surroundings. Optional 120V fan tray top-mounted and caster kit. Several APC Smart-UPS models low-profile provide easy UPS integration and mounting. 13U Wall mount cabinet, 19 inches maximum mounting depth, 200lb weight capacity, 19" rack width, ships fully assembled, glass door, 5 year APC warranty.

Main

Product or component type	Rack enclosure
Number of rack unit	13U
Number of cables	1
Provided equipment	Key(s) User manual Wall-mounting template

Physical

Height	663 mm
Width	584 mm
Depth	631 mm
Product weight	42.73 kg
Colour	Black
Mounting preference	No preference
Mounting mode	Not rack-mountable
Maximum mounting depth	482.6 mm
Rack width	19"
Marking	16 gauge EIA mounting rail 16 gauge front door 16 gauge post 13 gauge rear door 18 gauge roof 18 gauge side panels
Permanent permissible load	90.7 kg static

Conformance

Standards	EIA-310E

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downloaded from Arrow.com.

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	83.8 cm
Package 1 Width	68.6 cm
Package 1 Length	77.5 cm
Package 1 Weight	52.16 kg

Contractual warranty

Warranty (in months)	60

Downloaded from Arrow.com.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Environmental footprint

Total lifecycle Carbon footprint	**183 kg CO2 eq.**
Carbon footprint of the manufacturing phase [A1 to A3]	**175 kg CO2 eq.**
Carbon footprint of the distribution phase [A4]	**4 kg CO2 eq.**
Carbon footprint of the installation phase [A5]	**0 kg CO2 eq.**
Carbon footprint of the use phase [B2, B3, B4, B6]	**0 kg CO2 eq.**
Carbon footprint of the end-of-life phase [C1 to C4]	**4 kg CO2 eq.**
Environmental Disclosure	Product Environmental Profile

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
EU RoHS Directive	Compliant
REACh Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension

Repair	**No**

Use Again

Repack and remanufacture

Recyclability potential, in %	**95**
End of life manual availability	**No need of specific recycling operations**
Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins**

Downloaded from Arrow.com.

Image of product / Alternate images

Alternative





Downloaded from Arrow.com.