



Pushing Performance
Since 1945

PP-V14-CC-IDC-RJ45-4P-P-M-STR-SHLD




Image is for illustration purposes only. Please refer to product description.

Part number	09 35 229 0401
Specification	PP-V14-CC-IDC-RJ45-4P-P-M-STR-SHLD
HARTING eCatalogue	https://b2b.harting.com/09352290401

Identification

Category	Connectors
Series	Han® PushPull (V14)
Element	Connector
Specification	AIDA compliant PROFINET Straight

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	4
Coding	RJ45
Details	When installing a PROFINET system, observe the PROFINET installation guideline.

Technical characteristics

Conductor cross-section	0.12 ... 0.32 mm² Stranded 0.12 ... 0.32 mm² Solid
Conductor cross-section	AWG 26/7 ... AWG 22/7 Stranded AWG 24/1 ... AWG 22/1 Solid
Wire outer diameter	0.8 ... 1.6 mm
Transmission characteristics	Cat. 5 Class D up to 100 MHz
Data rate	10 Mbit/s 100 Mbit/s
Limiting temperature	-40 ... +85 °C



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP65 IP67
Cable diameter	5 ... 8 mm

Material properties

Surface (contacts)	Au over Ni Mating side Sn over Ni Termination side
Material (hood/housing)	Zinc die-cast
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol
ECHA SCIP number	5b0b428a-c671-4c90-9b6d-16804ea5737a
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60603-7 Mating face ISO/IEC 11801 EN 50173-1 IEC 61076-3-117 Variant 14
Approvals	DNV GL
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	94 g
Country of origin	Latvia
European customs tariff number	85366990
GTIN	5713140224292
eCl@ss	27440114 Rectangular connector (for field assembly)