




[+ HARNESSING](#)  
[HEAT SHRINK BOOTS](#)



✓ Active

TE CONNECTIVITY (TE)  
**202D174-12-0**  
[Raychem](#) | [CAP](#) , [CRPS](#)

202D174-12-0  
TE Internal Number: 811089-000  
Alias ID: 4-1196303-5

[EU RoHS Compliant](#)  
[EU ELV Compliant](#)

**Lipped** Yes

**Operating Temperature Range (°C)** -55 – 200

**Fluid/Chemical Resistance** Suitable for long term fluid immersion & elevated temperatures including fuel

**Adhesive Options** S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F), S1255-04 Separate Adhesive, -55°C – 200°C (-67°F – 392°F)

**Material Systems Code** 200

[↓](#) **PRODUCT DRAWING**  
English

DOCUMENTATION

Product Drawings

**Boot, Straight, With Lips**  
PDF  
**English**

Product Specifications

Product Specification

**Raychem Fluoro Elastomer Molded Components Flame-Retarded, Flexible, Heat-Shrinkable**  
PDF  
**English**

Product Environmental Compliance

Safety Data Sheet

Heat-Shrinkable Fluoropolymer Products

PDF

English

Heat-Shrinkable Fluoropolymer Products

PDF

German

Heat-Shrinkable Fluoropolymer Products

PDF

French

Heat-Shrinkable Fluoropolymer Products

PDF

Dutch

Heat-Shrinkable Fluoropolymer Products

PDF

Italian

Heat-Shrinkable Fluoropolymer Products

PDF

Spanish

Heat-Shrinkable Fluoropolymer Products

PDF

Swedish

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Molded Part Type   Molded Boot

Configuration Features

Lipped   Yes

Body Features

Material Systems Code   200

Adhesive Pre-Coat   No

Entry Size (Braided or Magneform Adapter)   20, 22, 24

Entry Size (Solid or Fixed Adapter)   16 – 18

Material   Modified Fluoro-Elastomer

Entry Size (Tinel-Lock Adapter)   18, 20, 22, 24

Entry Size (Spin Coupling Adapter)   20 – 24

Dimensions

Cable Diameter Range   15.7 – 35.3 mm [ .618 – 1.39 in ]

Wire/Cable Outside Diameter   .7 in, .71 in, .787 in, .87 in, .9 in, .94 in, 1 in, 1.02 in, 18 mm, 20 mm, 22 mm, 24 mm, 26 mm

Usage Conditions

**Operating Temperature Range (°C)** -55 – 200

Operation/Application

**Power Cable Accessory** No

Industry Standards

**Government Qualified** No

**Approved Standards** BS-G-198-5-DD, DEF Std 59-97 Issue 3 Type DD, SAE AS I 81765/4

Other

**Fluid/Chemical Resistance** Suitable for long term fluid immersion & elevated temperatures including fuel

**Adhesive Options** S1125 Separate Adhesive, -75°C – 150°C (-103°F – 302°F), S1255-04 Separate Adhesive, -55°C – 200°C (-67°F – 392°F)

**Adhesive Type** Adhesive Purchased Separately

Statement of Compliance

**Statement of Compliance**

PDF