




NOTE:

- ① NICHELATURA SU TUTTA LA SUPERFICIE -
- ② 0,76 μ m SPESS. ORO SOLO NELL'AREA FUNZIONALE **F** -
- ③ 0,38 μ m SPESS ORO SOLO NELL'AREA FUNZIONALE **F** -
- ④ FLASH DI ORO SU TUTTO IL TERMINALE -
- ⑤ 2,54 μ m SPESS. STAGNO NELL'AREA **G** -
- ⑥ RESTRICTED -

NOT FOR SALES
OUTSIDE ITALY

SEZIONE - AA -

SEZIONE - BB -

SEZIONE - CC -

①	③	⑤	INACTIVE	182029-5
①	②	⑤		182029-4
①	③	④		182029-3 ⑥
①	②	④		182029-2 ⑥
FINITURA -			PART NUMBER -	

H	OBSOLETE P/N-3 ECR 06-23380	AV	03
G	REVISIO WIRE BARREL DIM. S. ETOO-010-9-11/10/75		93
F	RIVISTE TOLLERANZE	VP	8/89
E	Aggiunto nota ⑥	EB	22-9-87
D	REVISIO PER ECN I-1661	B	23-1-84
C	AGGIORN. FINIT. P.N. -45-5	DR	18-11-82
B	AGGIUNTE VARIANTI -45-5	DR	2-10-81
A	RELEASED FOR PRODUCTION 1609	DR	16-12-76
LTR	REVISION RECORD	DR	CHK - DATE

NUMBER

		DWG SIZE	NUMBER	NAME	REMARKS		ITEM NO.	
REQUIRED PER ASSEMBLY			(C) 10 BY AMP INCORPORATED. ALL RIGHTS RESERVED. AMP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.			CUSTOMER COPY REFERENCE ONLY		
DR			Fioravino 30 th 9-75		MATER: BRONZO FOSFOROSO		 AMP ITALIA S.p.A. Corso F.lli Cervi, 15 COLLEGNO (TORINO)	
CHK			Barro 8 th 10-75		FINITURA: VEDERE TABELLA		CLASS	
DE			Estello 15/10/75		WIRE - RANGE - INSULATION		TYPE	
AMP			Scavini 21/6/75		0.012-0.026 mm 1.29-2.03 mm TOLERANCE EXCEPT AS NOTED ±0.3 ± 1.0		SCALE 10:1	
DESCRIPTION					DOC I		NO D	
					C-182029		H	
					AMP - LEAF CONTACT		- LOOSE PIECE	