

Detailed Specifications

Frame Width:	35[mm]
Frame Height:	35[mm]
Frame Length:	51[mm]
Steps per Rev.:	200
Step Angle:	1.80[degrees]
Drive Sequence:	bipolar
Drive Voltage:	24[V]
Rated Current per Phase:	1.50[A]
Resistance:	2.20[Ohms]
Inductance:	3.70[mH]
Holding Torque:	400[mN-m]
Detent Torque:	13.70[mN-m]
Mass:	290[g]
Rotor Inertia:	43[g-cm ²]

Standard Hybrid