DATASHEET

SMD ▪ B
16-219A/T2D-AQ1R2RX/3T



Features

- Package in 8mm tape on 7″ diameter reel.
- Compatible with automatic placement equipment.
- Compatible with infrared and vapor phase reflow solder process.
- Mono-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- The maximum height is 0.25mm
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

Description

- The 16-219A SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

Applications

- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General

Copyright © 2010, Everlight All Rights Reserved. Release Date :12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Device Selection Guide

Chip Materials	Emitted Color	Resin Color
InGaN	Pure White	Yellow Diffused

Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_R	5	V
Forward Current	I_F	10	mA
Peak Forward Current (Duty 1/10 @1KHz)	I_{FP}	20	mA
Power Dissipation	Pd	30	mW
Operating Temperature	T_{opr}	-40 ~ +85	℃
Storage Temperature	Tstg	-40 ~ +90	℃
Electrostatic Discharge	ESD_{HBM}	150	V
Soldering Temperature	T_{sol}	Reflow Soldering : 260 ℃ for 10 sec. Hand Soldering : 350 ℃ for 3 sec.	

Electro-Optical Characteristics (Ta=25℃)

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Luminous Intensity	Iv	72	-----	180	mcd	I_F=2mA
Viewing Angle	$2\theta_{1/2}$	-----	130	-----	deg	
Forward Voltage	V_F	2.5	----	3.1	V	
Reverse Current	I_R	-----	-----	50	μA	V_R=5V

Note:
1. Tolerance of Luminous Intensity: ±11%
2. Tolerance of Forward Voltage: ±0.05V

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
Q1	72	90	mcd	I_F =2mA
Q2	90	112		
R1	112	140		
R2	140	180		

Bin Range Of Luminous Voltage

Group	Bin Code	Min.	Max.	Unit	Condition
R	9	2.5	2.7	V	I_F =2mA
	10	2.7	2.9		
	11	2.9	3.1		

Note:
1. Tolerance of Luminous Intensity: ±11%
2. Tolerance of Forward Voltage: ±0.05V

EVERLIGHT

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Chromaticity Coordinates Specifications for Bin Grading

Group	Bin Code	CIE_X	CIE_Y	Condition
A	1	0.274	0.226	I_F =2mA
		0.274	0.258	
		0.294	0.286	
		0.294	0.254	
	2	0.274	0.258	
		0.274	0.291	
		0.294	0.319	
		0.294	0.286	
	3	0.294	0.254	
		0.294	0.286	
		0.314	0.315	
		0.314	0.282	
	4	0.294	0.286	
		0.294	0.319	
		0.314	0.347	
		0.314	0.315	
	5	0.314	0.282	
		0.314	0.315	
		0.334	0.343	
		0.334	0.311	
	6	0.314	0.315	
		0.314	0.347	
		0.334	0.376	
		0.334	0.343	


Notes:
1.The C.I.E. 1931 chromaticity diagram (Tolerance ±0.01).
2.The products are sensitive to static electricity and care must be fully taken when handling products.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.

CIE Chromaticity Diagram




Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)


Downloaded from Arrow.com.

Typical Electro-Optical Characteristics Curves


Spectrum Distribution




Forward Current vs. Forward Voltage




Luminous Intensity vs. Ambient Temperature




Luminous Intensity vs. Forward Current



Forward Current Derating Curve



Radiation Diagram





Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3


Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)


Downloaded from Arrow.com.

Package Dimension










Recommend Soldering pad




Suggested pad dimension is just for reference only.
Please modify the pad dimension based on individual need.

Note: Tolerances unless mentioned ±0.1mm. Unit = mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3 www.everlight.com
Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)
Downloaded from Arrow.com.


Moisture Resistant Packing Materials

Label Explanation



- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- LOT No: Lot Number

Reel Dimensions




Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)


Downloaded from Arrow.com.

Carrier Tape Dimensions: Loaded quantity 3000 PCS per reel



Note: The tolerances unless mentioned is ±0.1mm ,Unit = mm

Moisture Resistant Packaging




Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.


Precautions For Use

1. Over-current-proof
Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).
2. Storage
2.1 Do not open moisture proof bag before the products are ready to use.
2.2 Before opening the package: The LEDs should be kept at 30℃ or less and 90%RH or less.
2.3 After opening the package: The LED's floor life is 1 year under 30℃ or less and 60% RH or less.
If unused LEDs remain, it should be stored in moisture proof packages.
2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions.
Baking treatment : 60±5℃ for 24 hours.
3. Soldering Condition
3.1 Pb-free solder temperature profile



3.2 Reflow soldering should not be done more than two times.
3.3 When soldering, do not put stress on the LEDs during heating.
3.4 After soldering, do not warp the circuit board.
4.Soldering Iron
Each terminal is to go to the tip of soldering iron temperature less than 350℃ for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5.Repairing
Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.

Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

DISCLAIMER

1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

Copyright © 2010, Everlight All Rights Reserved. Release Date : 12-Dec-2016 Issue No: DSE-0013421 Rev.3

Ver.:3 Release Date:12/21/2016 狀態:Approved(正式發行)

Downloaded from Arrow.com.