



+ CONNECTORS

BOARD-TO-BOARD JUMPERS & SHUNTS



✓ Active

TE CONNECTIVITY (TE)  
2P, AMPMODU I SHUNT, GREEN  
AMPMODU

826853-2  
TE Internal Number: 826853-2

EU RoHS Compliant  
EU ELV Compliant

Shunt Style Open Top  
Number of Positions 2  
Centerline (Pitch) 3.96 mm [ .156 in ]

↓ PRODUCT DRAWING  
English

↓ 3D PDF

DOCUMENTATION

Product Drawings

SHUNT ASSEMBLY, MODU I, RASTER 3.96mm SHUNT KOMPLETT, MODU I, RASTER 3.96mm  
PDF (TIFF AVAILABLE)  
English

CAD Files

Customer View Model  
2D\_DXF.ZIP  
English

Customer View Model  
3D\_IGS.ZIP  
English

Customer View Model  
3D\_STP.ZIP

English

3D PDF

PDF

English

Agency Approvals

Agency Approval Document

AMPMODU CONNECTOR REPORT (GERMANY)

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Product Type Shunt

Configuration Features

Number of Positions 2

Body Features

Handle Without

Contact Features

Shunt Style Open Top

Contact Mating Area Plating Thickness 2 μm [ 78.74 μin ]

Shunt Type AMPMODU MOD I

Contact Base Material Cu Sn4

Contact Mating Area Plating Material Pre-Tin

Housing Features

Centerline (Pitch) 3.96 mm [ .156 in ]

Housing Material Polyamide 6.6 GF

Housing Color Green

Dimensions

Height 8 mm [ .315 in ]

Industry Standards

UL Rating Recognized

UL Flammability Rating UL 94-HB

CSA Certified Yes

Packaging Features

**Packaging Method** Bag

**Packaging Quantity** 500

**PRODUCT COMPLIANCE** 

Statement of Compliance

**Statement of Compliance**

PDF