LR1F47K5 Product Details



LR1F47K5
(1630887-1)
TE Internal Number: 1630887-1
Active

Fixed Resistors

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Fixed Resistor
- Resistor Type = General Purpose Resistor
- Resistance Selection = K Ω
- Resistance = 47.5K Ω
- Power Rating = .60 W

View all Features

Add to My Part List | Request Sample | Find Similar Products | Buy Product

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Documentation & Additional Information

Product Drawings:
- None Available

Catalog Pages/Data Sheets:
- 1309350_PASSIVE_COMPONENT (PDF, English)
- Metal Film Fixed Resistors - Type LR Series - Tyco E... (PDF, English)

Product Specifications:
- None Available

Application Specifications:
- None Available

Instruction Sheets:
- None Available

CAD Files:
- None Available

List all Documents

Additional Information:
- Product Line Information

Related Products:
- Tooling

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:
- Product Type = Fixed Resistor
- Resistor Type = General Purpose Resistor
- Element = Thin Film
- Series = LR
- Termination Type = Tinned Copper Leads

Electrical Characteristics:
- Resistance Selection (Ω) = K
- Resistance (Ω) = 47.5K
- Power Rating (W) = 0.60
- Tolerance (%) = 1
- Package Type = Ammo Packed

Body Features:
- Mount Style = Axial Leaded
- Package, Component Size = 6.2 x 2.3

Configuration Features:
- Number of Terminations = 2
- Number of Resistors = 1

Industry Standards:
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
- Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Converted to comply with RoHS directive

Conditions for Usage:
- Temperature Coefficient (ppm/°C) = ±50

Operation/Application:
- Application = Semi Precision

Other:
- Brand = Neohm

© 2012 Tyco Electronics Corporation, a TE Connectivity Ltd. company. All Rights Reserved | Privacy Policy

Provide Website Feedback

Downloaded from Arrow.com.