

MK 3/8**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image** Similar to illustration

Multi-pole terminal strips are suitable for wiring in junction boxes and small distribution boxes. The different numbers of poles offer the possibilities of direct mounting inside the housings.

General ordering data

Version	Single- and multi-pole terminal strip, Screw connection, medium yellow, 2.5 mm ² , 24 A, 400 V, Number of connections: 16, Number of levels: 1
Order No.	0274420000
Type	MK 3/8
GTIN (EAN)	4008190185015
Qty.	25 ST

Technical data

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E60693
Certificate No. (cURusEX)	E184763

Dimensions and weights

Depth	16.1 mm	Depth (inches)	0.6339 inch
Height	15 mm	Height (inches)	0.5906 inch
Width	72.75 mm	Width (inches)	2.8642 inch
Net weight	25.94 g		

Temperatures

Storage temperature	-25 °C...55 °C	Ambient temperature	-5 °C...40 °C
Continuous operating temp., min.	-60 °C	Continuous operating temp., max.	130 °C

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Material data

Material	KrG	Colour	medium yellow
UL 94 flammability rating	5VA		

System specifications

Version	For the mounting rails	End cover plate required	No
Number of potentials	1	Number of levels	1
Rail	Mounting plate		

Additional technical data

Installation advice	Direct mounting	Explosion-tested version	No
Type of mounting	Direct mounting		

CSA rating data

Wire cross section max. (CSA)	12 AWG	Voltage size C (CSA)	300 V
Current size C (CSA)	25 A	Certificate No. (CSA)	12400-149
Wire cross section min. (CSA)	22 AWG		

Conductors for clamping (additional connection)

Connection type, additional connection	Screw connection
--	------------------

Technical data

Conductors for clamping (rated connection)

Gauge to IEC 60947-1	A2	Wire connection cross section AWG, max.	AWG 12
Connection direction	on side	Tightening torque, max.	0.45 Nm
Tightening torque, min.	0.4 Nm	Stripping length	5 mm
Type of connection 2	Screw connection	Type of connection	Screw connection
Number of connections	16	Clamping range, max.	4 mm ²
Clamping range, min.	0.33 mm ²	Clamping screw	M 2.5
Blade size	0.6 x 3.5 mm	Wire connection cross section AWG, min.	AWG 22
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, max.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/4, min.	0.5 mm ²
Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, max.	1.5 mm ²	Wire connection cross-section, finely stranded with wire-end ferrules DIN 46228/1, min.	0.5 mm ²
Wire connection cross section, finely stranded, max.	2.5 mm ²	Wire connection cross section, finely stranded, min.	0.5 mm ²
Connection cross-section, stranded, max.	2.5 mm ²	Connection cross-section, stranded, min. 1.5 mm ²	
Torque level with DMS electric screwdriver	1	Wire connection cross-section, solid core, max.	4 mm ²
Wire connection cross-section, solid core, min.	0.5 mm ²		

Dimensions

Fixing dimension	18.5 mm
------------------	---------

General

Number of poles	8	Wire connection cross section AWG, max.	AWG 12
Installation advice	Direct mounting	Wire connection cross section AWG, min.	AWG 22
Standards	IEC 60947-7-1	Rail	Mounting plate

Rating data

Rated cross-section	2.5 mm ²	Rated voltage	400 V
Rated DC voltage	400 V	Rated current	24 A
Current at maximum wires	24 A	Standards	IEC 60947-7-1
Volume resistance according to IEC 60947-7-x	1.33 mΩ	Rated impulse withstand voltage	6 kV
Power loss in accordance with IEC 60947-7-x	0.77 W	Pollution severity	3

UL rating data


Voltage size B (UR)	300 V	Current size B (UR)	20 A
Conductor size Factory wiring max. (UR)	12 AWG	Current size D (UR)	5 A
Conductor size Factory wiring min. (UR)	22 AWG	Certificate No. (UR)	E60693
Conductor size Field wiring min. (UR)	22 AWG	Voltage size D (UR)	600 V
Conductor size Field wiring max. (UR)	12 AWG		

Classifications

ETIM 6.0	EC001284	ETIM 7.0	EC001284
ETIM 8.0	EC001284	ETIM 9.0	EC001284

Technical data

ETIM 10.0	EC001284	ECLASS 9.0	27-14-11-06
ECLASS 9.1	27-14-11-06	ECLASS 10.0	27-14-11-06
ECLASS 11.0	27-14-11-06	ECLASS 12.0	27-14-11-06
ECLASS 13.0	27-14-11-06	ECLASS 14.0	27-14-11-06
ECLASS 15.0	27-14-11-06		

Accessories**QB MK**

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Type	QB 2 MK3	Version
Order No.	3833700000	Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 2,
GTIN (EAN)	4008190542535	Pitch in mm (P): 10.00, Insulated: Yes, Width: 14.5 mm
Qty.	20 ST	
Type	QB 4 MK3	Version
Order No.	3833800000	Cross-connector (terminal), Plugged, black, 24 A, Number of poles: 4,
GTIN (EAN)	4008190542542	Pitch in mm (P): 10.00, Insulated: Yes, Width: 33.5 mm
Qty.	20 ST	