



© 2019 TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	PROPOSED	19NOV2020	-	-
	2	REVISED PANEL CUT-OUT	14MAY2021	DF	DR
	3	ADD DUST CAP	02JUL2021	CG	DR
	4	ADD NICKEL PTFE ASSEMBLIES	30JAN2023	CG	DR
	A	RELEASED PER ECN-23-223284	26JUL2023	MM	DR













45 DEGREE
INSERT OPTION

1. FINISH: OLIVER DRAB, CADMIUM.
2. FINISH: NICKEL, ELECTROLESS
3. REFERENCE MIL-DTL-38999 SPECIFICATION FOR PANEL NUT INSTALLATION TORQUE VALUE.
4. FINISH: NICKEL PTFE



RECOMMENDED PANEL CUT-OUT 3



KEYING ORIENTATION DETAIL

KEYING ORIENTATION	A	B	C	D
N	95°	141°	208°	236°
A	113°	156°	182°	292°
B	90°	145°	195°	252°

FINISH (SHELL AND NUT)	KEYING ORIENTATION SEE DETAIL	INSERT ORIENTATION	ASSEMBLY PART NUMBER
NICKEL PTFE 4	B	45°	1-2379812-8
NICKEL PTFE 4	B	-	1-2379812-7
NICKEL PTFE 4	A	45°	1-2379812-6
NICKEL PTFE 4	A	-	1-2379812-5
NICKEL PTFE 4	N	45°	1-2379812-4
NICKEL PTFE 4	N	-	1-2379812-3
NICKEL 2	B	45°	1-2379812-2
NICKEL 2	B	-	1-2379812-1
OLIVE DRAB 1	B	45°	1-2379812-0
OLIVE DRAB 1	B	-	2379812-9
NICKEL 2	A	45°	2379812-8
NICKEL 2	A	-	2379812-7
OLIVE DRAB 1	A	45°	2379812-6
OLIVE DRAB 1	A	-	2379812-5
NICKEL 2	N	45°	2379812-4
NICKEL 2	N	-	2379812-3
OLIVE DRAB 1	N	45°	2379812-2
OLIVE DRAB 1	N	-	2379812-1

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±-
1 PLC ±-
2 PLC ±0.13
3 PLC ±0.013
4 PLC ±-
ANGLES ±1

MATERIAL - / -

FINISH - / -

DWN D. FABIAN 19NOV2020
CHK -
APVD -
PRODUCT SPEC -
APPLICATION SPEC -
WEIGHT -

TE Connectivity

NAME KIT, RECEPTACLE CONNECTOR ASSEMBLY FIBER OPTIC, MT, SIZE 15, 4 CAVITY 38999 STYLE, PANEL MOUNT

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A1	00779	C-2379812	-

CUSTOMER DRAWING | SCALE 2:1 | SHEET 1 OF 1 | REV A

4805 (3/13)

Downloaded from Arrow.com.