

RFA6T-74SP3-74SP3-0300

RFA6T, RFB6T SERIES

75 Ω OPTIMIZED BNC CABLE ASSEMBLIES

SPECIFICATIONS

For complete specifications
see www.samtec.com?RFA6T
or www.samtec.com?RFB6T

RF Connector:

Outer Contact Material:
Ni plated Brass (BNC),
Au plated BeCu (DIN),
Au plated Phosphor Bronze
(HDBNC)

Center Contact Material:
Gold plated Brass

Insulator Material:
PTFE

Operating Temperature:
-65 °C to +125 °C

Impedance:

75 Ω ± 3 Ω (-ST)

75 Ω ± 4 Ω (-RA)

Frequency Range:
0-3.5 GHz *

Working Voltage:
500 Vrms max *

Dielectric Withstanding:
1500 Vrms min *

RoHS Compliant:
Yes

RG 6/1694A Cable:

Impedance:

75 Ω ± 3 Ω

Capacitance:

54 ± 3 pF/meter

Max Attenuation

(cable only):

0.21 dB @ 1 GHz for 1 meter

Conductor Size:

18 AWG, (1.02 mm) .040" dia.

Conductor Material:

Bare Copper

Insulator Material:

Gas Injected Foamed

Polyethylene

Shield Material:

Tinned Copper Braid over

Aluminum Foil Wrap

Jacket Material:

PVC

Jacket Diameter:

(7.00 mm) .275"

Bend Radius: 69.85 mm

Jacket Color: Black

RoHS Compliant: Yes


Mates with:
BNC7T, DIN7A, HDBNC



Solutionator
DESIGN IN A MINUTE

- Create a full system:
cable assembly and board level mates,
50 Ω and 75 Ω solutions
- Free samples available
- Visit: rf.samtec.com

18 AWG 75 Ω
RG 6 coax cable,
or 1694A Belden cable




ALSO AVAILABLE
(MOQ Required)

- Additional stripping
and tinning options
- Additional plating options

OTHER SOLUTIONS

- Hand tool available.
Contact RFGroup@samtec.com
- Cable connector kits
(see cable components catalog pages)







* See connector component
pages for specific range.



STRIPPED & TINNED (Dimensions in mm)

CALLOUT	A	B	C
-303030	3.0	3.0	3.0
-303040	3.0	3.0	4.0
-403030	4.0	3.0	3.0
-403040	4.0	3.0	4.0
-404040	4.0	4.0	4.0

Both center conductor and
braid shield are stripped,
only the center
conductor is tinned.

END OPTIONS		END OPTIONS	
-H4SP3 = 75 Ω High-Density BNC Straight Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		-74RP3 = 75 Ω BNC Right-angle Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)	
-78SP4 = 75 Ω DIN Straight Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		-SING = Single Ended (End 2 callout)	
-74SP3* = 75 Ω BNC Straight Plug (10 μ" (0.25 μm) Gold on Center Contact, Nickel on Shell)		-XXXXXX = Stripped & Tinned (End 2 callout) (See chart for callout)	
(*Die Cast also available = -D4SP3)			

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Components must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.