

Features

- Halogen Free. "Green" Device (Note 1)
- Lead Free Finish/RoHS Compliant ("P" Suffix designates RoHS Compliant.)
- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- No External Components Required
- Epoxy Meets UL 94 V-0 Flammability Rating


Maximum Ratings

Parameter	Symbol	Value	Unit
Input Voltage	V_I	30	V
Maximum Output Current	I_O	0.1	A
Power Dissipation	P_d	0.35	W
Operating Junction Temperature	T_{OPR}	-25~125	°C
Storage Temperature Range	T_{STG}	-55~150	°C

Note: 1. Halogen free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.


Marking code: 78L05FA

Schematic Diagram




Three-Terminal Low Current Positive Voltage Regulator

SOT-89



DIMENSIONS					
DIM	INCHES		MM		NOTE
	MIN	MAX	MIN	MAX	
A	0.169	0.185	4.30	4.70	
B	0.061		1.55		TYP.
C	0.154	0.171	3.91	4.35	
D	0.031	0.047	0.80	1.20	
E	0.089	0.104	2.25	2.65	
F	0.118		3.00		TYP.
G	0.013	0.020	0.33	0.52	
H	0.015	0.021	0.38	0.53	
J	0.014	0.017	0.35	0.44	
K	0.055	0.063	1.40	1.60	
L	0.059		1.50		TYP.

Suggested Solder Pad Layout



Electrical Characteristics($V_I=10V$, $I_O=40mA$, $C_I=0.33\mu F$, $C_O=0.1\mu F$, unless otherwise specified)

Parameter	Symbol	Test conditions	Min	Typ	Max	Unit
Output Voltage	V_O	$V_I=7V-20V$ $I_O=1mA-40mA$ $T_J=25^\circ C$	4.8	-	5.2	V
		$V_I=10V$ $I_O=100mA$ $T_J=25^\circ C$	4.75	-	5.25	V
Load Regulation	ΔV_O	$I_O=1mA-100mA$, $T_J=25^\circ C$,	-0.06	-	0.06	V
		$I_O=1mA-40mA$, $T_J=25^\circ C$	-0.03	-	0.03	V
Line regulation	ΔV_O	$V_I=7V-20V$, $T_J=25^\circ C$	-0.15	-	0.15	V
		$V_I=8V-20V$, $T_J=25^\circ C$	-0.1	-	0.1	V
Quiescent Current	I_q	$V_I=10V$, $I_O=40mA$	-	-	5.5	mA
Quiescent Current Change	ΔI_q	$V_I=8V-20V$, $I_O=40mA$	-0.15	-	0.15	mA
		$V_I=10V$, $I_O=1mA-40mA$	-0.1	-	0.1	mA

Curve Characteristics

Fig. 1 - Output Characteristics




Fig. 2 - Quiescent Current vs Input Voltage




Fig. 3 - Current Cut-off Grid Voltage





Fig. 4 - Power Derating Curve



Ordering Information

Device	Packing
Part Number-TP	Tape&Reel:1Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications, enhancements, improvements, or other changes. **Micro Commercial Components Corp.** does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights, nor the rights of others. The user of products in such applications shall assume all risks of such use and will agree to hold **Micro Commercial Components Corp.** and all the companies whose products are represented on our website, harmless against all damages. **Micro Commercial Components Corp.** products are sold subject to the general terms and conditions of commercial sale, as published at <https://www.mccsemi.com/Home/TermsAndConditions>.

LIFE SUPPORT

MCC's products are not authorized for use as critical components in life support devices or systems without the express written approval of Micro Commercial Components Corporation.

CUSTOMER AWARENESS

Counterfeiting of semiconductor parts is a growing problem in the industry. Micro Commercial Components (MCC) is taking strong measures to protect ourselves and our customers from the proliferation of counterfeit parts. MCC strongly encourages customers to purchase MCC parts either directly from MCC or from Authorized MCC Distributors who are listed by country on our web page cited below. Products customers buy either from MCC directly or from Authorized MCC Distributors are genuine parts, have full traceability, meet MCC's quality standards for handling and storage. **MCC will not provide any warranty coverage or other assistance for parts bought from Unauthorized Sources.** MCC is committed to combat this global problem and encourage our customers to do their part in stopping this practice by buying direct or from authorized distributors.