

## MM74HC148

### 8-3 Line Priority Encoder

#### General Description

The MM74HC148 priority encoder utilizes advanced silicon-gate CMOS technology. It has the high noise immunity and low power consumption typical of CMOS circuits, as well as the speeds and output drive similar to LB-TTL.

This priority encoder accepts 8 input request lines 0–7 and outputs 3 lines A0–A2. The priority encoding ensures that only the highest order data line is encoded. Cascading circuitry (enable input EI and enable output EO) has been provided to allow octal expansion without the need for external circuitry. All data inputs and outputs are active at the low logic level.

All inputs are protected from damage due to static discharge by internal diode clamps to  $V_{CC}$  and ground.


#### Features

- Typical propagation delay: 13 ns
- Wide supply voltage range: 2V–6V

#### Ordering Code:

| Order Number | Package Number | Package Description                                                          |
|--------------|----------------|------------------------------------------------------------------------------|
| MM74HC148M   | M16A           | 16-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow |
| MM74HC148N   | N16E           | 16-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide       |

#### Connection Diagram




#### Truth Table


| EI | Inputs |   |   |   |   |   |   |   | Outputs |    |    |    |    |
|----|--------|---|---|---|---|---|---|---|---------|----|----|----|----|
|    | 0      | 1 | 2 | 3 | 4 | 5 | 6 | 7 | A2      | A1 | A0 | GS | EO |
| H  | X      | X | X | X | X | X | X | X | H       | H  | H  | H  | H  |
| L  | H      | H | H | H | H | H | H | H | H       | H  | H  | H  | L  |
| L  | X      | X | X | X | X | X | X | L | L       | L  | L  | L  | H  |
| L  | X      | X | X | X | X | X | L | H | L       | L  | H  | L  | H  |
| L  | X      | X | X | X | X | L | H | H | L       | H  | L  | L  | H  |
| L  | X      | X | X | X | L | H | H | H | H       | L  | L  | L  | H  |
| L  | X      | X | L | H | H | H | H | H | H       | L  | H  | L  | H  |
| L  | X      | L | H | H | H | H | H | H | H       | H  | L  | L  | H  |
| L  | L      | H | H | H | H | H | H | H | H       | H  | H  | L  | H  |

H = HIGH  
L = LOW  
X = Irrelevant

## Schematic Diagram



## Logic Diagram



**Absolute Maximum Ratings** (Note 1)

(Note 2)

|                                                  |                         |
|--------------------------------------------------|-------------------------|
| Supply Voltage ( $V_{CC}$ )                      | -0.5 to +7.0V           |
| DC Input Voltage ( $V_{IN}$ )                    | -1.5 to $V_{CC} + 1.5V$ |
| DC Output Voltage ( $V_{OUT}$ )                  | -0.5 to $V_{CC} + 0.5V$ |
| Clamp Diode Current ( $I_{IK}, I_{OK}$ )         | $\pm 20$ mA             |
| DC Output Current, per pin ( $I_{OUT}$ )         | $\pm 25$ mA             |
| DC $V_{CC}$ or GND Current, per pin ( $I_{CC}$ ) | $\pm 50$ mA             |
| Storage Temperature Range ( $T_{STG}$ )          | -65°C to +150°C         |
| Power Dissipation ( $P_D$ )                      |                         |
| (Note 3)                                         | 600 mW                  |
| S.O. Package only                                | 500 mW                  |
| Lead Temperature ( $T_L$ )                       |                         |
| (Soldering 10 sec.)                              | 260°C                   |

**Operation Conditions**

|                                                     | Min | Max      | Units |
|-----------------------------------------------------|-----|----------|-------|
| Supply Voltage ( $V_{CC}$ )                         | 2   | 6        | V     |
| DC Input or Output Voltage<br>( $V_{IN}, V_{OUT}$ ) | 0   | $V_{CC}$ | V     |
| Operating Temperature Range ( $T_A$ )               |     |          |       |
| MM74HC                                              | -40 | +85      | °C    |
| MM54HC                                              | -55 | +125     | °C    |
| Input Rise or Fall Times<br>( $t_r, t_f$ )          |     |          |       |
| $V_{CC} = 2.0V$                                     |     | 1000     | ns    |
| $V_{CC} = 4.5V$                                     |     | 500      | ns    |
| $V_{CC} = 6.0V$                                     |     | 400      | ns    |

**Note 1:** Absolute Maximum Ratings are those values beyond which damage to the device may occur.

**Note 2:** Unless otherwise specified all voltages are referenced to ground.

**Note 3:** Power Dissipation temperature derating—plastic "N" package: -12 mW/°C from 65°C to 85°C.

**DC Electrical Characteristics** (Note 4)

| Symbol          | Parameter                                | Conditions                                                                                                           | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | T <sub>A</sub> = −40 to 85°C |      | T <sub>A</sub> = −55 to 125°C |  | Units |
|-----------------|------------------------------------------|----------------------------------------------------------------------------------------------------------------------|-----------------|-----------------------|-------------------|------------------------------|------|-------------------------------|--|-------|
|                 |                                          |                                                                                                                      |                 | Typ                   | Guaranteed Limits |                              |      |                               |  |       |
| V <sub>IH</sub> | Minimum HIGH Level Input Voltage         |                                                                                                                      | 2.0V            |                       | 1.5               | 1.5                          | 1.5  | V                             |  |       |
|                 |                                          |                                                                                                                      | 4.5V            |                       | 3.15              | 3.15                         | 3.15 | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            |                       | 4.2               | 4.2                          | 4.2  | V                             |  |       |
| V <sub>IL</sub> | Maximum LOW Level Input Voltage (Note 5) |                                                                                                                      | 2.0V            |                       | 0.5               | 0.5                          | 0.5  | V                             |  |       |
|                 |                                          |                                                                                                                      | 4.5V            |                       | 1.35              | 1.35                         | 1.35 | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            |                       | 1.8               | 1.8                          | 1.8  | V                             |  |       |
| V <sub>OH</sub> | Minimum HIGH Level Output Voltage        | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 2.0                   | 1.9               | 1.9                          | 1.9  | V                             |  |       |
|                 |                                          |                                                                                                                      | 4.5V            | 4.5                   | 4.4               | 4.4                          | 4.4  | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            | 6.0                   | 5.9               | 5.9                          | 5.9  | V                             |  |       |
|                 |                                          | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4.0 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA | 4.5V            | 4.7                   | 3.96              | 3.84                         | 3.7  | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            | 5.2                   | 5.48              | 5.34                         | 5.2  | V                             |  |       |
|                 |                                          |                                                                                                                      |                 |                       |                   |                              |      |                               |  |       |
| V <sub>OL</sub> | Maximum LOW Level Output Voltage         | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 20 μA                                  | 2.0V            | 0                     | 0.1               | 0.1                          | 0.1  | V                             |  |       |
|                 |                                          |                                                                                                                      | 4.5V            | 0                     | 0.1               | 0.1                          | 0.1  | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            | 0                     | 0.1               | 0.1                          | 0.1  | V                             |  |       |
|                 |                                          | V <sub>IN</sub> = V <sub>IH</sub> or V <sub>IL</sub><br> I <sub>OUT</sub>   ≤ 4.0 mA<br> I <sub>OUT</sub>   ≤ 5.2 mA | 4.5V            | 0.2                   | 0.26              | 0.33                         | 0.4  | V                             |  |       |
|                 |                                          |                                                                                                                      | 6.0V            | 0.2                   | 0.26              | 0.33                         | 0.4  | V                             |  |       |
|                 |                                          |                                                                                                                      |                 |                       |                   |                              |      |                               |  |       |
| I <sub>IN</sub> | Maximum Input Current                    | V <sub>IN</sub> = V <sub>CC</sub> or GND                                                                             | 6.0V            |                       | ±0.1              | ±1.0                         | ±1.0 | μA                            |  |       |
| I <sub>CC</sub> | Maximum Quiescent Supply Current         | V <sub>IN</sub> = V <sub>CC</sub> or GND<br>I <sub>OUT</sub> = 0 μA                                                  | 6.0V            |                       | 8.0               | 80                           | 160  | μA                            |  |       |

**Note 4:** For a power supply of 5V  $\pm 10\%$  the worst case output voltages ( $V_{OH}$  and  $V_{OL}$ ) occur for HC at 4.5V. Thus the 4.5V values should be used when designing with this supply. Worst case  $V_{IH}$  and  $V_{IL}$  occur at  $V_{CC} = 5.5V$  and 4.5V respectively. (The  $V_{IH}$  value at 5.5V is 3.85V.) The worst case leakage current ( $I_{IN}$ ,  $I_{CC}$ , and  $I_{OZ}$ ) occur for CMOS at the higher voltage and so the 6.0V values should be used.

**Note 5:**  $V_{IL}$  limits are currently tested at 20% of  $V_{CC}$ .

## AC Electrical Characteristics

| Symbol             | Parameter                                             | Conditions | Typ | Guaranteed Limits | Units |
|--------------------|-------------------------------------------------------|------------|-----|-------------------|-------|
| $t_{PHL}, t_{PLH}$ | Maximum Propagation Delay,<br>Any Input to Any Output |            | 14  |                   | ns    |


## AC Electrical Characteristics

$V_{CC} = 2.0V$  to  $6.0V$ ,  $C_L = 50$  pF,  $t_r = t_f = 6$  ns (unless otherwise specified)


| Symbol                              | Parameter                                 | V <sub>CC</sub> | T <sub>A</sub> = 25°C |                   | −40°C to +85°C | −55°C to +125°C | Units |
|-------------------------------------|-------------------------------------------|-----------------|-----------------------|-------------------|----------------|-----------------|-------|
|                                     |                                           |                 | Typ                   | Guaranteed Limits |                |                 |       |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Inputs 0–7<br>to Outputs<br>A0, A1, A2    | 2.0V            |                       | 140               | 175            | 210             | ns    |
|                                     |                                           | 4.5V            | 14                    | 28                | 35             | 42              | ns    |
|                                     |                                           | 6.0V            |                       | 24                | 30             | 36              | ns    |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Inputs 0–7<br>to<br>Output EO             | 2.0V            |                       | 140               | 175            | 210             | ns    |
|                                     |                                           | 4.5V            | 15                    | 28                | 35             | 42              | ns    |
|                                     |                                           | 6.0V            |                       | 24                | 30             | 36              | ns    |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Inputs 0–7<br>to<br>Output GS             | 2.0V            |                       | 160               | 200            | 240             | ns    |
|                                     |                                           | 4.5V            | 17                    | 32                | 40             | 48              | ns    |
|                                     |                                           | 6.0V            |                       | 27                | 34             | 41              | ns    |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Input EI<br>to Outputs<br>A0, A1, A2      | 2.0V            |                       | 160               | 200            | 240             | ns    |
|                                     |                                           | 4.5V            | 17                    | 32                | 40             | 48              | ns    |
|                                     |                                           | 6.0V            |                       | 27                | 34             | 41              | ns    |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Input EI<br>to<br>Output GS               | 2.0V            |                       | 100               | 125            | 150             | ns    |
|                                     |                                           | 4.5V            | 12                    | 20                | 25             | 30              | ns    |
|                                     |                                           | 6.0V            |                       | 17                | 21             | 26              | ns    |
| t <sub>PHL</sub> , t <sub>PLH</sub> | Input EI<br>to<br>Output EO               | 2.0V            |                       | 100               | 125            | 150             | ns    |
|                                     |                                           | 4.5V            | 12                    | 20                | 25             | 30              | ns    |
|                                     |                                           | 6.0V            |                       | 17                | 21             | 26              | ns    |
| t <sub>r</sub> , t <sub>f</sub>     | Maximum<br>Output Rise<br>and Fall Time   | 2.0V            |                       | 75                | 95             | 110             | ns    |
|                                     |                                           | 4.5V            | 7                     | 15                | 19             | 22              | ns    |
|                                     |                                           | 6.0V            |                       | 13                | 16             | 19              | ns    |
| C <sub>pd</sub>                     | Power Dissipation<br>Capacitance (Note 6) |                 | 52                    |                   |                |                 | pF    |
| C <sub>in</sub>                     | Maximum Input<br>Capacitance              |                 | 5                     | 10                | 10             | 10              | pF    |

**Note 6:**  $C_{pd}$  determines the no load dynamic power consumption, and the no load dynamic current consumption.

# Physical Dimensions inches (millimeters) unless otherwise noted



16-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow  
Package Number M16A



**16-Lead Plastic Dual-In-Line Package (PDIP), JEDEC MS-001, 0.300" Wide  
Package Number N16E**

Fairchild does not assume any responsibility for use of any circuitry described, no circuit patent licenses are implied and Fairchild reserves the right at any time without notice to change said circuitry and specifications.

## LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF THE PRESIDENT OF FAIRCHILD SEMICONDUCTOR CORPORATION. As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury to the user.
  2. A critical component in any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.
- www.fairchildsemi.com**

www.fairchildsemi.com