




Automotive Parts > Automotive Connector Accessories > Automotive Connector Caps & Covers



Number of Positions: 31

Primary Product Color: **Black**

Protection & Strain Relief Accessory Type: **Cover**

Primary Product Material: **PA 66**

Cable Exit Angle: **90 °**

Features

Product Type Features

Sealable	No
Protection & Strain Relief Accessory Type	Cover

Configuration Features

Number of Positions	31
---------------------	----

Body Features

Primary Product Color	Black
Primary Product Material	PA 66
Cable Exit Angle	90 °

Mechanical Attachment

Strain Relief	Without
---------------	---------

Usage Conditions

Operating Temperature (Max)	100 °C[212 °F]
Operating Temperature Range	-40 – 100 °C[-40 – 212 °F]

Industry Standards

UL Flammability Rating	UL 94HB
------------------------	---------

Packaging Features

Packaging Method	Box
------------------	-----

Other



Serviceable	Yes
-------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	有害物质含量符合标准要求 No Restricted Substance(s) Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2025 (250) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 953042-9 31W HYB TIMER CONN ASSY	TE Part # 953041-3 31W HYB TIMER CONN ASSY	TE Part # 953041-2 31W HYB TIMER CONN ASSY	TE Part # 1-953042-7 31W HYB TIMER CONN ASSY
---	---	---	---






TE Part # 1-953041-4
31W HYB TIMER CONN ASSY




TE Part # 953042-6
31W HYB TIMER CONN ASSY



TE Part # 953042-2
31W HYB TIMER CONN ASSY



TE Part # 953041-8
31W HYB TIMER CONN



TE Part # 953041-1
21W HYB TIMER CONN ASSY



TE Part # 953042-3
31W HYB TIMER CONN ASSY




TE Part # CAT-T4827-CH8172
Timer Connector Housing

Also in the Series

Timer Connector System




Automotive Connector Caps & Covers
(12)




Automotive Housings(187)



Automotive Signal & Power Headers
(21)



Automotive Terminals(112)



Other Automotive Connector
Accessories(1)



Quick Disconnects(4)

Customers Also Bought



TE Part #1011-231-0305
BKSHL, 3P, BLK, PLG, ST, NW6/7.5/8.5 /10



TE Part #1-953042-6
31W HYB TIMER CONN



Documents

Product Drawings

VERTIC COVER 31W HYB CONN

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_953040-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_953040-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_953040-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

CONNECTEUR 31 VOIES ABS POUR CONTACT MICRO-TIMER II ET STANDARD-POWER-TIMER

English

Product Specification

English

Instruction Sheets

Instruction Sheet (non U.S.)

French