Part Number : 513534000
Product Description : MicroClasp Receptacle Housing, 2.00mm Pitch, Positive Lock, Dual Row, 40 Circuits, White
Series Number : 51353
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

513534000_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

561340000-AS-000.pdf

SPK-51353-001-001.pdf

PS-51353-003-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

Downloaded from Arrow.com.

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	51353
Description	MicroClasp Receptacle Housing, 2.00mm Pitch, Positive Lock, Dual Row, 40 Circuits, White
Application	Wire-to-Board
Component Type	Receptacle
Product Name	MicroClasp
UPC	800756611174

Agency

UL	E29179

Physical

Circuits (maximum)	40
Color - Resin	White
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1714.000/mg
Number of Rows	2

Downloaded from Arrow.com.

Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Stackable	No
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
MicroClasp Vertical Dual Row Headers	501844
MicroClasp Vertical Dual Row Headers	55917
MicroClasp Right-Angle Dual Row Headers	55959

Use with Part(s)

Description	Part Number
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 150.00mm Length, 24 AWG, Black	797581001
Pre-Crimped Lead MicroClasp Female-to-MicroClasp Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black	797581002
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG, Copper Alloy, Reel	561349000
MicroClasp 2.00mm Pitch and MUO 2.5 Crimp Terminal, Female, Tin (Sn) Plated, 28-22 AWG, Copper Alloy, Bag	561349100
Micro-One 2.0 Female Crimp Terminals	224041
MicroClasp Terminal Position Assurance (TPA) Retainers	500638

Downloaded from Arrow.com.

Downloaded from Arrow.com.