

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

- ? Header
- ? Header Type = Breakaway
- ? Number of Rows = Single
- ? Number of Positions = 4
- ? Mating Post Length = 5.80 mm

[View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

? [AMPMODU II STIFTLEISTEN, EINREIHIG](#) (PDF, German)

? None Available

? None Available

? None Available

? None Available

- ? 2D Drawing (DXF, Version O)
- ? 3D Model (IGES, Version O)
- ? 3D Model (STEP, Version O)

? Product Line Information

? Tooling

List all Documents

Product Type Features:

- ? Product Type = Header
- ? Number of Positions = 4
- ? Mount Angle = Vertical
- ? PCB Retention Feature = No
- ? Surface Mount Compatible = No
- ? Board Standoff = Without
- ? Mounting Ears = Without
- ? Mating Connector Lock = Without
- ? Profile = Standard

? **Mating Post Length (mm [in]) = 5.80 [0.228]**
 ? Panel Attachment = Without

? Termination (Solder) Post Length (mm [in]) = 3.20 [0.126]

? Solder Tail Contact Plating = Tin

? Header Type = Breakaway
 ? Number of Rows = Single
 ? Centerline, Matrix (mm [in]) = 2.54 [.100]
 ? Selectively Loaded = No
 ? Mount Type = PC Board

? Contact Mating Area Plating Material = Gold
(30)

? Contact Material = Phosphor Bronze

? Housing Material = Thermoplastic Polyester
? Housing Flammability Rating = UL 94V -0

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? High Temperature Housing = No

? High Speed Serial Data Connector = No

? Brand = AMP