MOSFET - Power, Single N-Channel, STD Gate, µ8FL

40 V, 1.9 mΩ, 141 A

NVTFWS1D9N04XM

$V_{(BR)DSS}$	$R_{DS(ON)}$ MAX	I_D MAX
40 V	1.9 mΩ @ V_{GS} = 10 V	141 A


Features


- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- Small Footprint (3.3 x 3.3 mm) for Compact Design
- AEC-Q101 Qualified and PPAP Capable
- These Devices are Pb-Free, Halogen Free/BFR Free and are RoHS Compliant

Applications

- Motor Drive
- Battery Protection
- Synchronous Rectification


N-CHANNEL MOSFET





WDFNW8
(Full–Cut µ8FL WF)
CASE 515AN

MARKING DIAGRAM



XXXXX = Specific Device Code
A = Assembly Location
Y = Year
WW = Work Week
▪ = Pb-Free Package

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)

Parameter		Symbol	Value	Unit
Drain–to–Source Voltage		V_{DSS}	40	V
Gate–to–Source Voltage		V_{GS}	±20	V
Continuous Drain Current	T_C = 25°C	I_D	141	A
	T_C = 100°C		100	
Power Dissipation	T_C = 25°C	P_D	74	W
Pulsed Drain Current	T_A = 25°C, t_p = 10 µs	I_{DM}	852	A
Operating Junction and Storage Temperature Range		T_J, T_{stg}	−55 to +175	°C
Continuous Source–Drain Current (Body Diode)		I_S	104	A
Single Pulse Avalanche Energy ($I_{L(pk)}$ = 8.5 A)		E_{AS}	286	mJ
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)		T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS

Parameter	Symbol	Value	Unit
Thermal Resistance, Junction–to–Case	$R_{\theta JC}$	2.0	°C/W
Thermal Resistance, Junction–to–Ambient	$R_{\theta JA}$	47	

© Semiconductor Components Industries, LLC, 2024

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition	Min	Typ	Max	Unit
OFF CHARACTERISTICS						
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 1 mA, T_J = 25°C	40			V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$\Delta V_{(BR)DSS}/\Delta T_J$	I_D = 1 mA, Referenced to 25°C		15		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{DS} = 40 V, T_J = 25°C			1	μA
		V_{DS} = 40 V, T_J = 125°C			20	
Gate−to−Source Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = 20 V			100	nA
ON CHARACTERISTICS						
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V, I_D = 15 A, T_J = 25°C		1.6	1.9	mΩ
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 70 μA, T_J = 25°C	2.5		3.5	V
Threshold Temperature Coefficient	$\Delta V_{GS(TH)}/\Delta T_J$	V_{GS} = V_{DS}, I_D = 70 μA		−7		mV/°C
Forward Transconductance	g_{FS}	V_{DS} = 5 V, I_D = 15 A		81		S
CHARGES AND CAPACITANCES						
Input Capacitance	C_{ISS}	V_{DS} = 25 V, V_{GS} = 0 V, f = 1 MHz,		1882		pF
Output Capacitance	C_{OSS}			1211		
Reverse Transfer Capacitance	C_{RSS}			20		
Total Gate Charge	$Q_{G(TOT)}$	V_{DD} = 32 V, I_D = 15 A, V_{GS} = 10 V		30		nC
Threshold Gate Charge	$Q_{G(TH)}$			6		nC
Gate−to−Source Charge	Q_{GS}			8		
Gate−to−Drain Charge	Q_{GD}			6		
Gate Resistance	R_G	f = 1 MHz		0.90		Ω
SWITCHING CHARACTERISTICS						
Turn−On Delay Time	$t_{d(ON)}$	Resistive Load, V_{GS} = 10 V, V_{DD} = 32 V, I_D = 15 A, R_G = 0 Ω		7		ns
Rise Time	t_r			14		
Turn−Off Delay Time	$t_{d(OFF)}$			10		
Fall Time	t_f			18		
DRAIN−SOURCE DIODE CHARACTERISTICS						
Forward Diode Voltage	V_{SD}	I_S = 15 A, V_{GS} = 0 V, T_J = 25°C		0.78	1.2	V
		I_S = 15 A, V_{GS} = 0 V, T_J = 125°C		0.63		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, I_S = 15 A, dIs/dt = 100 A/μs, V_{DD} = 32 V, T_J = 25°C		42		ns
Charge Time	t_a			17		
Discharge Time	t_b			25		
Reverse Recovery Charge	Q_{RR}			38		nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On−Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On−Resistance vs. Gate Voltage




Figure 4. On−Resistance vs. Drain Current




Figure 5. Normalized ON Resistance vs. Junction Temperature




Figure 6. Drain Leakage Current vs. Drain Voltage

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Characteristics




Figure 8. Gate Charge Characteristics




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Characteristics




Figure 11. Safe Operating Area (SOA)




Figure 12. Avalanche Current vs. Pulse Time (UIS)

Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 13. Transient Thermal Response

ORDERING INFORMATION

Device	Marking	Package Type	Shipping†
NVTFWS1D9N04XMTAG	1D9W	WDFN8 (Pb-Free)	1500 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.


Share Feedback
Your Opinion Matters

Downloaded from Arrow.com.


PACKAGE DIMENSIONS

WDFNW8 3.3x3.3, 0.65P (Full−Cut μ8FL WF)
CASE 515AN
ISSUE O

NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 2009.
2. CONTROLLING DIMENSION: MILLIMETERS
3. DIMENSION D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.




TOP VIEW




DETAIL A


DIM	MILLIMETERS		
	MIN.	NOM.	MAX.
A	0.70	0.75	0.80
A1	0.00	----	0.05
b	0.23	0.30	0.40
c	0.15	0.20	0.25
D	3.05	3.30	3.55
D1	2.95	3.05	3.15
D2	1.98	2.11	2.24
E	3.05	3.30	3.55
E1	2.95	3.05	3.15
E2	1.47	1.60	1.73
E3	0.23	0.30	0.40
e	0.65 BSC		
G	0.30	0.41	0.51
K	0.65	0.80	0.95
L	0.30	0.43	0.59
L1	0.06	0.13	0.20
M	1.40	1.50	1.60




SIDE VIEW



DETAIL B



BOTTOM VIEW



RECOMMENDED MOUNTING FOOTPRINT

* For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.