THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

LED1 POLARITY			LED2 POLARITY		
PIN 11	PIN 12	COLOR	PIN 13	PIN 14	COLOR
-	+	YELLOW	-	+	YELLOW
+	-	GREEN	+	-	GREEN

RoHS 2002/95/EC

ELECTRICAL CHARACTERISTICS @ 25°C

TURNS RATIO

TP1	1CT : 1CT ±2%
TP2	1CT : 1CT ±2%
TP3	1CT : 1CT ±2%
TP4	1CT : 1CT ±2%

OCL @ 100kHz/100mVRMS

8mA DC BIAS	350µH MIN.

INS. LOSS

100KHz TO 125MHz	-1.2 dB MAX

RET. LOSS (MIN)

0.5MHz-40MHz	-18 dB
40MHz-100MHz	-12+20LOG(f/80MHz) dB

CROSS TALK:

Ch1-Ch2,Ch1-Ch3,Ch1-Ch4,Ch2-Ch3,Ch2-Ch4,Ch3-Ch4

1MHz - 30MHz	-35 dB MIN
30MHz - 80MHz	-24 dB MIN
80MHz - 100MHz	-25 dB MIN

CM TO CM REJ

100kHz - 100MHz	-30 dB MIN

CM TO DM REJ

100kHz - 100MHz	-35 dB MIN


HIPOT (Isolation Voltage): 1500 Vrms

100% OF PRODUCTION TESTED TO COMPLY WITH IEEE 802.3 ISOLATION REQUIREMENTS.


OPERATING TEMPERATURE RANGE: -40 TO +85°C

LED 1 AND LED 2

VF (FORWARD VOLTAGE)	IF=20mA	GREEN	2.2V TYP.
		YELLOW	2.1V TYP.
λD (DOMINANT WAVELENGTH)	IF=20mA	GREEN	565nm TYP.
		YELLOW	590nm TYP.



SCHEMATIC



ORIGINATED BY: CHOW WANCHUNG	DATE: 07-11-08	TITLE: Gigabit MagJack® WITH LED Extend Temp.	PART NO. / DRAWING NO.: SI-61025-F	STANDARD DIM. TOL. IN INCH: .X, .XX, .XXX	[ ] METRIC DIM. AS REFERENCE
DRAWN BY: LI YONGFENG	DATE: 07-11-08		FILE NAME: SI-61025-F_A.DWG		UNIT : INCH [mm] / REV. : A
					SCALE : N/A / SIZE : A4
					PAGE : 2

bel COMPONENTS FOR A CONNECTED PLANET


This document is electronically generated. This is a controlled copy if used internally


Downloaded from Arrow.com.


Please read our datasheet & drawing disclaimer here.

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS 2002/95/EC







NOTES:

PLASTIC HOUSING: THERMOPLASTIC PBT
FLAMMABILITY RATING UL 94V-0

CONTACTS PLATING: 50 MICRO-INCH HARD GOLD PLATING

PINS: TIN-COATED COPPER WIRE, DIA 0.018 INCH.

METAL SHIELD: NICKEL PLATED ON COPPER ALLOY.
(ALL GROUND LEADS ARE SOLDER DIPPED)

1. MARK PART WITH MFG PART NUMBER(SI-61025-F), DATE CODE.
2. MARK PART WITH MFG LOGO, MFG NAME.
3. JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS
4. RoHS COMPLIANCE, PER EU DIRECTIVE 2002/95/EC.

c UL us UL RECOGNIZED - FILE #E132408.


ORIGINATED BY: BILL CHEN	DATE: 07-11-08	TITLE: Gigabit MagJack® WITH LED Extend Temp.	PART NO. / DRAWING NO.: SI-61025-F	STANDARD DIM. TOL. IN INCH: .X, .XX, .XXX ±0.010	[ ] METRIC DIM. AS REFERENCE	bel COMPONENTS FOR A CONNECTED PLANET
DRAWN BY: SALLY LUO	DATE: 07-11-08		FILE NAME: SI-61025-F_A.DWG		UNIT : INCH [mm] REV. : A SCALE : N/A SIZE : A4 PAGE : 3	

This document is electronically generated. This is a controlled copy if used internally

Downloaded from Arrow.com.

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS 2002/95/EC



RECOMMENDED PCB FOOTPRINT
COMPONENT SIDE VIEW

ORIGINATED BY: BILL CHEN	DATE: 07-11-08	TITLE: Gigabit MagJack® WITH LED Extend Temp.	PART NO. / DRAWING NO.: SI-61025-F	STANDARD DIM. TOL. IN INCH: .X, .XX, .XXX ±0.004	[ ] METRIC DIM. AS REFERENCE	bel COMPONENTS FOR A CONNECTED PLANET
DRAWN BY: SALLY LUO	DATE: 07-11-08		FILE NAME: SI-61025-F_A.DWG		UNIT : INCH [mm] REV. : A SCALE : N/A SIZE : A4 PAGE : 4	


This document is electronically generated. This is a controlled copy if used internally

Downloaded from Arrow.com.

THE INFORMATION CONTAINED HEREIN IS CONSIDERED "PROPRIETARY" TO BEL FUSE INC. AND SHALL NOT BE COPIED, REPRODUCED OR DISCLOSED WITHOUT THE WRITTEN APPROVAL OF BEL FUSE INC.

RoHS 2002/95/EC

SUGGESTED PANEL OPENING



NOTES:

THE DISTANCE OF PANEL INSIDE SURFACE RELATIVE TO FRONT SURFACE OF PART IS ONLY A SUGGESTION. IN CASE THIS DISTANCE IS DIFFERENT, THE REQUIRED PANEL OPENING DIMENSIONS CHANGE ACCORDINGLY.

PACKING INFORMATION

PACKING TRAY : 0200-9999-Q7 (TOP)
0200-9999-Q8 (BOTTOM)

PACKING QUANTITY : 80 PCS FINISHED GOODS PER TRAY
10 TRAYS (800 PCS FINISHED GOODS) PER CARTON BOX

NOTE : CARDBOARDS ARE PLACED BETWEEN LAYERS OF PACKING TRAY INSIDE CARTON BOX (INCLUDE THE UPPERMOST AND LOWERMOST TRAY)

ORIGINATED BY: BILL CHEN	DATE: 07-11-08	TITLE: Gigabit MagJack® WITH LED Extend Temp.	PART NO. / DRAWING NO.: SI-61025-F	STANDARD DIM. TOL. IN INCH: .X, .XX, .XXX ±0.004	[ ] METRIC DIM. AS REFERENCE
DRAWN BY: SALLY LUO	DATE: 07-11-08		FILE NAME: SI-61025-F_A.DWG		UNIT : INCH [mm] / REV. : A
					SCALE : N/A / SIZE : A4
					PAGE : 5

bel COMPONENTS FOR A CONNECTED PLANET

This document is electronically generated. This is a controlled copy if used internally

Downloaded from Arrow.com.