




IP140MA SERIES
IP140M SERIES
IP78M00A SERIES
IP78M00 SERIES



Pin 1 – V_{IN}
Pin 2 – V_{OUT}
Case – Ground

H Package – TO-39

**SMD 1
CERAMIC SURFACE MOUNT**



8 Pin J Package

Order Information

Part Number	H-Pack (TO-39)	J-Pack CERDIP	SG-Pack SMD	Temp. Range
IP78MxxAzz	✓	✓	✓	-55 to +150°C
IP78Mxxxx	✓	✓	✓	"
IP140MAzz-xx	✓		✓	"
IP140Mzz-xx	✓		✓	"

Note:

xx = Voltage Code (05, 12, 15)
eg. IP78M05J

zz = Package Code (H, J, SG)
IP140MAH-12

FEATURES

- OUTPUT CURRENT UP TO 0.5A
- OUTPUT VOLTAGES OF 5, 12, 15V
- 0.01% / V LINE REGULATION
- 0.3% / A LOAD REGULATION
- THERMAL OVERLOAD PROTECTION
- SHORT CIRCUIT PROTECTION
- OUTPUT TRANSISTOR SOA PROTECTION
- 1% VOLTAGE TOLERANCE (-A VERSIONS)

DESCRIPTION

The IP140MA and IP78M00A series of voltage regulators are fixed output regulators intended for local, on-card voltage regulation. These devices are available in 5, 12, and 15 volt options and are capable of delivering in excess of 500mA over temperature.

The A-suffix devices are fully specified at 0.5A, provide 0.01% / V line regulation, 0.3% / A load regulation, and $\pm 1\%$ output voltage tolerance at room temperature. Protection features include safe operating area, current limiting and thermal shutdown.

ABSOLUTE MAXIMUM RATINGS ($T_C = 25^\circ\text{C}$ unless otherwise stated)

V_I	DC Input Voltage (for $V_O = 5, 12, 15V$)	35V
P_D	Power Dissipation	Internally limited ¹
$R_{\theta JC}$	Thermal Resistance Junction to Case – H Package	20°C / W
$R_{\theta JC}$	Thermal Resistance Junction to Case – SG Package	TBA °C / W
$R_{\theta JA}$	Thermal Resistance Junction to Ambient – J Package	119°C / W
T_J	Operating Junction Temperature Range	–55 to 150°C
T_{stg}	Storage Temperature	–65 to 150°C

Note 1. Although power dissipation is internally limited, these specifications are applicable for maximum power dissipation P_{MAX} of 2W for the H-Package ,1.05W for the J-Package and 15W for the SG-Package.

Semelab plc. Telephone +44(0)1455 556565. Fax +44(0)1455 552612.
E-mail: sales@semelab.co.uk Website: <http://www.semelab.co.uk>

Prelim 7/00

ELECTRICAL CHARACTERISTICS

Parameter	Test Conditions	IP78M05A IP140MA-05			IP78M05 IP140M-05			Units	
		Min.	Typ.	Max.	Min.	Typ.	Max.		
V _O Output Voltage	I _O = 100mA V _{IN} = 10V	4.95	5	5.05	4.8	5	5.2	V	
	I _O = 5mA to 350mA P _D ≤ P _{MAX} V _{IN} = 7.5V to 20V T _J = -55 to 150°C	4.85		5.15	4.75		5.25		
ΔV _O Line Regulation	I _O = 200mA	V _{IN} = 7V to 25V	3	10			50	mV	
		V _{IN} = 8V to 25V T _J = -55 to 150°C	3	10			25		
	I _O = 500mA	V _{IN} = 8V to 12V	3	10			50		
ΔV _O Load Regulation	I _O = 5mA to 500mA V _{IN} = 10V T _J = -55 to 150°C		5	50			50	mV	
I _Q Quiescent Current	V _{IN} = 10V I _O = 350mA T _J = -55 to 150°C		4	6		4	6	mA	
ΔI _Q Quiescent Current Change	I _O = 5mA to 500mA V _{IN} = 10V T _J = -55 to 150°C		0.1	0.5			0.5	mA	
	I _O = 200mA V _{IN} = 8V to 25V T _J = -55 to 150°C		0.2	0.8			0.8		
V _N Output Noise Voltage	f = 10Hz to 100kHz		40	200		40	200	μV	
ΔV _{IN} ΔV _O	Ripple Rejection	f = 120Hz V _{IN} = 8V to 18V	I _O = 300mA	65	80	62		dB	
			I _O = 100mA T _J = -55 to 150°C	65	80	62			
Dropout Voltage	I _O = 350mA		2	2.5			2.5	V	
I _{sc} Short Circuit Current	V _{IN} = 35V		300	600		300	600	mA	
I _{pk} Peak Output Current	V _{IN} = 10V		0.7	1.0	1.4	0.7	1.0	1.6	A
Average Temperature Coefficient of V _O	I _O = 5mA		0.5	2.0		0.5		mV / °C	

1) All characteristics are measured with a capacitor across the input of 0.22μF and a capacitor across the output of 0.1μF.

All characteristics except noise voltage and ripple rejection ratio are measured using pulse techniques (t_p ≤ 10ms, δ ≤ 5%). Output voltage changes due to changes in internal temperature must be taken into account separately.

2) Test Conditions unless otherwise stated: T_J = 25°C

P_{MAX} = 2W for H Package (TO-39)

P_{MAX} = 1.05W for J Package (CERDIP)

P_{MAX} = 15W for SG Package (SMD1)

ELECTRICAL CHARACTERISTICS

Parameter	Test Conditions	IP78M12A IP140MA-12			IP78M12 IP140M-12			Units
		Min.	Typ.	Max.	Min.	Typ.	Max.	
V _O Output Voltage	I _O = 100mA V _{IN} = 19V	11.88	12	12.12	11.50	12	12.50	V
	I _O = 5mA to 350mA P _D ≤ P _{MAX} V _{IN} = 14.8V to 27V T _J = -55 to 150°C	11.64		12.36	11.40		12.60	
ΔV _O Line Regulation	I _O = 200mA V _{IN} = 14.5V to 30V V _{IN} = 16V to 30V T _J = -55 to 150°C	4	18		60			mV
		4	18		30			
	I _O = 500mA V _{IN} = 16V to 22V	4	18		120			
ΔV _O Load Regulation	I _O = 5mA to 500mA V _{IN} = 19V T _J = -55 to 150°C	10	60		120			mV
I _Q Quiescent Current	V _{IN} = 19V I _O = 350mA T _J = -55 to 150°C	4	6		4	6		mA
ΔI _Q Quiescent Current Change	I _O = 5mA to 500mA V _{IN} = 19V T _J = -55 to 150°C	0.1	0.5		0.5			mA
	I _O = 200mA V _{IN} = 14.8V to 30V T _J = -55 to 150°C	0.2	0.8		0.8			
V _N Output Noise Voltage	f = 10Hz to 100kHz	75	480		75	480		μV
ΔV _{IN} ΔV _O Ripple Rejection	f = 120Hz V _{IN} = 15V to 25V	I _O = 300mA	58	72	55			dB
		I _O = 100mA T _J = -55 to 150°C	58	72	55			
Dropout Voltage	I _O = 350mA	2	2.5		2.5			V
I _{sc} Short Circuit Current	V _{IN} = 35V	300	600		300	600		mA
I _{pk} Peak Output Current	V _{IN} = 19V	0.7	1.0	1.4	0.7	1.0	1.6	A
Average Temperature Coefficient of V _O	I _O = 5mA	1.2	4.8		1.2			mV / °C

1) All characteristics are measured with a capacitor across the input of 0.22μF and a capacitor across the output of 0.1μF.

All characteristics except noise voltage and ripple rejection ratio are measured using pulse techniques (t_p ≤ 10ms, δ ≤ 5%). Output voltage changes due to changes in internal temperature must be taken into account separately.

2) Test Conditions unless otherwise stated: T_J = 25°C

P_{MAX} = 2W for H Package (TO-39)

P_{MAX} = 1.05W for J Package (CERDIP)

P_{MAX} = 15W for SG Package (SMD1)

ELECTRICAL CHARACTERISTICS

Parameter	Test Conditions	IP78M15A IP140MA-15			IP78M15 IP140M-15			Units	
		Min.	Typ.	Max.	Min.	Typ.	Max.		
V _O Output Voltage	I _O = 100mA V _{IN} = 23V	14.85	15	15.15	14.40	15	15.60	V	
	I _O = 5mA to 350mA P _D ≤ P _{MAX} V _{IN} = 18V to 30V T _J = -55 to 150°C	14.55		15.45	14.25		15.75		
ΔV _O Line Regulation	I _O = 200mA	V _{IN} = 17.5V to 30V	4	22			60	mV	
		V _{IN} = 20V to 30V T _J = -55 to 150°C	4	22			30		
	I _O = 500mA	V _{IN} = 20V to 26V	4	22			150		
ΔV _O Load Regulation	I _O = 5mA to 500mA V _{IN} = 23V T _J = -55 to 150°C		12	75			150	mV	
I _Q Quiescent Current	V _{IN} = 23V	I _O = 350mA T _J = -55 to 150°C	4	6			4	6	mA
ΔI _Q Quiescent Current Change	I _O = 5mA to 500mA V _{IN} = 23V T _J = -55 to 150°C		0.1	0.5			0.5	mA	
	I _O = 200mA V _{IN} = 18V to 30V T _J = -55 to 150°C		0.2	0.8			0.8		
V _N Output Noise Voltage	f = 10Hz to 100kHz		90	600			90	600	μV
ΔV _{IN} ΔV _O	f = 120Hz V _{IN} = 18.5V to 28.5V	I _O = 300mA	57	70			54	dB	
		I _O = 100mA T _J = -55 to 150°C	57	70			54		
Dropout Voltage	I _O = 350mA		2	2.5			2.5	V	
I _{sc} Short Circuit Current	V _{IN} = 35V		300	600			300	600	mA
I _{pk} Peak Output Current	V _{IN} = 23V		0.7	1.0	1.4	0.7	1.0	1.6	A
Average Temperature Coefficient of V _O	I _O = 5mA		1.5	6.0			1.5		mV / °C

1) All characteristics are measured with a capacitor across the input of 0.22μF and a capacitor across the output of 0.1μF.

All characteristics except noise voltage and ripple rejection ratio are measured using pulse techniques (t_p ≤ 10ms, δ ≤ 5%). Output voltage changes due to changes in internal temperature must be taken into account separately.

2) Test Conditions unless otherwise stated: T_J = 25°C

P_{MAX} = 2W for H Package (TO-39)

P_{MAX} = 1.05W for J Package (CERDIP)

P_{MAX} = 15W for SG Package (SMD1)