



Surface Mount Fast Switching Rectifier

Reverse Voltage 50 to 800 V

Forward Current 1.0 A



Mounting Pad Layout



Features

- Plastic package has Underwriters Laboratory Flammability Classification 94V-0
- Low profile surface mount package
- Built-in strain relief
- Fast switching for high efficiency
- Glass passivated chip junction
- High temperature soldering: 250°C/10 seconds at terminals

Mechanical Data

Case: JEDEC DO-214AC molded plastic over glass passivated chip

Terminals: Solder plated, solderable per MIL-STD-750, Method 2026

Polarity: Color band denotes cathode end

Weight: 0.002 ounce, 0.064 gram

Maximum Ratings & Thermal Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

Parameters	Symbols	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	Units
Device marking code		RA	RB	RD	RG	RJ	RK	
Maximum repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	V
Maximum RMS voltage	V_{RMS}	35	70	140	280	420	500	V
Maximum DC blocking voltage	V_{DC}	50	100	200	400	600	800	V
Maximum average forward rectified current at $T_L=90^\circ\text{C}$	$I_{F(AV)}$	1.0						A
Peak forward surge current 8.3ms single half sine-wave superimposed on rated load (JEDEC Method) $T_L=90^\circ\text{C}$	I_{FSM}	30						A
Maximum thermal resistance (NOTE 1)	$R_{\theta JA}$ $R_{\theta JL}$	105 32						°C/W
Operating junction and storage temperature range	T_J, T_{STG}	-55 to +150						°C

Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.

	Symbols	RS1A	RS1B	RS1D	RS1G	RS1J	RS1K	Units
Maximum instantaneous forward voltage at 1.0A	V_F	1.30						V
Maximum DC reverse current $T_A=25^\circ\text{C}$ at rated DC blocking voltage $T_A=125^\circ\text{C}$	I_R	5.0 50						μA
Maximum reverse recovery time at $I_F=0.5\text{A}$, $I_R=1.0\text{A}$, $I_{rr}=0.25\text{A}$	t_{rr}	150				250	500	ns
Typical junction capacitance at 4.0V, 1MHz	C_J	10				7.0		pF

NOTES: (1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2 x 0.2" (5.0 x 5.0mm) copper pad areas

Surface Mount Fast Switching Rectifier

Ratings and Characteristic Curves ($T_A = 25^\circ\text{C}$ unless otherwise noted)

