

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION






© COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
AF	50	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REV PER 0G3A-0696-03	04NOV03	JR	GP
			E1	REVISED PER ECO-10-000443	18JAN10	KK	HMR
			E2	REVISED PER ECR-12-021718	18DEC12	F.M	YHM

- 1 INSULATED HEATER WIRE: #18-16 AWG.
HEATER WIRE CORE DIA: 1.02 MAX
- 2 REF CRIMP INFO: WIRE BBL .090, F TYPE
INSULATION BBL .120, F TYPE
- 3 TRAVERSE WINDING ON METAL REEL.
- 4 IN-LINE WINDING ON A CARDBOARD REEL
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



R 0.58

R 1.02

5 OBSOLETE	7,500	4.44	3.8	3	#14-12 AWG	PRE-TIN	1438246-6
	5,000	4.44	3.8	4	#14-12 AWG	-	1438246-5
	5,000	3.18	3.3	4	#18-16 AWG	-	1438246-4
	7,500	4.44	3.8	3	#14-12 AWG	-	1438246-3
	5,000	3.18	3.3	4	#18-16 AWG	PRE-TIN	1438246-2
	12,500	3.18	3.3	3	#18-16 AWG	-	1438246-1
	PCS/REEL	"L "	"A"	NOTES	STD. WIRE SIZE	FINISH	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN	21MAY2002		 Tyco Electronics Corporation Harrisburg, PA 17105				
				B.P							
				CHK	21MAY02		NAME				
				F.M							
				APVD	21MAY02		SPLICE, BUTT, HEATER WIRE				
				YH.M							
				PRODUCT SPEC			—				
				—							
				APPLICATION SPEC			—				
				—							
				SIZE	CAGE CODE	DRAWING NO			RESTRICTED TO		
				A2		00779	C-1438246			—	
				CUSTOMER DRAWING			SCALE		10:1	SHEET	1 of 1
										REV	E2