

V23009A1007A100 Product Details



V23009A1007A100
(6-1393800-8)

TE Internal Number: 6-1393800-8

Active

Communications/Signal PC Board Relays

Converted to EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- V23008, V23009/Power Relay 15 Series
- DC Actuating System
- Input Voltage = 24 VDC
- Contact Arrangement = 3 Form C, 3PDT, 3 C/O
- Contact Current Rating = 8 A

View all Features

Quick Links

- Check Pricing & Availability
- Search for Tooling
- Product Feature Selector
- Contact Us About This Product

Add to My Part List Request Sample Find Similar Products Buy Product

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- Product Line Information

Related Products:

- Tooling

Product Features (Please use the Product Drawing for all design activity)

- Product Type Features:**
- Termination Type = Solder/Plug-In Terminals
- Electrical Characteristics:**
- Actuating System = DC
 - Input Voltage (VDC) = 24
 - Contact Current Rating (A) = 8
 - Coil Resistance (Ω) = 300
 - Coil Power, Nominal (mW) = 2000
 - Dielectric Between Coil and Contacts (V rms) = 2500
- Body Related Features:**
- Series = V23008, V23009/Power Relay 15
 - Polarized = No
- Contact Related Features:**
- Mounting Options = Socket
 - Enclosure Type = Dust Protected
 - FCC Part 68 Isolation = No
 - Approved Standards = None
 - Contact Base Material = Silver
 - Approx. Dimensions (L x W x H) (mm [in]) = 53.00 x 46.50 x 61.00 [2.087 x 1.831 x 2.402]
 - Compatible Socket = Without
 - Contact Type = Single
 - Pin Configuration = Industry Standard

- Configuration Related Features:**
- Contact Arrangement = 3 Form C, 3PDT, 3 C/O
 - Coil Magnetic System = Non Polarized, Monostable
 - Coil Suppression Diode = Without
- Industry Standards:**
- RoHS/ELV Compliance = RoHS compliant, ELV compliant
 - Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
 - RoHS/ELV Compliance History = Converted to comply with RoHS directive
- Other:**
- Brand = Axicom

BOOKMARK

Corporate Information

Who We Are
Investors
News Room
Supplier Portal
Careers

Quick Links

Check Distributor Inventory
Cross Reference
Find Documents & Drawings
Product Compliance Support Center
Site Map

Customer Support

Email or Chat with Us
Find a Phone Number
Search Knowledge Base
Manage Your Account

Sign up for our eNewsletter

Enter your email address

Follow us on: