




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**
Contact Mating Area Plating Material: **Gold (Au)**
Wire Contact Termination Area Plating Material: **Gold**
Operating Voltage: **600 VDC**

Features

Product Type Features

Discrete Wire Type	Stranded
--------------------	----------

Electrical Characteristics

Operating Voltage	600 VDC
-------------------	---------

Contact Features

Barrel Type	Open
Contact Type	Socket
Contact Mating Area Plating Material	Gold (Au)
Wire Contact Termination Area Plating Material	Gold
Contact Retention Within Housing	With
Contact Base Material	Brass
Contact Current Rating (Max)	7 A
Mating Pin Diameter	1 mm[.039 in]
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Material Finish	Matte



Contact Orientation	Straight
Contact Underplating Material	Nickel

Termination Features

Termination Method to Wire & Cable	Crimp
Product Terminates To	Wire & Cable

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	.3 – .89 mm²
Compatible Insulation Diameter Range	3.4 mm[.134 in]

Usage Conditions

Operating Temperature Range	-20 – 105 °C[-4 – 221 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	4000
Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-172336-2 UNIVERSAL MATE-N-LOK PLUG 2P	 TE Part # 2151030-2 OCEAN_2.0_APPLICATOR-S-062F110F-RSA	 TE Part # 172171-1 15 CIR UNIV M-N-L PLUG	 TE Part # 172162-1 12 CIR UNIV M-N-L CAP
 TE Part # 1-172159-2 MINI UNIVERSAL M-N-L CAP 4P	 TE Part # 1-172158-6 MINI-U-M-N-L 3P CAP BLUE	 TE Part # 1-172336-6 UNIVERSAL MATE-N-LOK PLUG 2P	 TE Part # 1-172158-2 MINI-U-M-N-L 3P CAP RED
 TE Part # 2305570-1 Strip Terminal Cutter-Side Feed-No Crimp	 TE Part # 770586-1 22P MINI UMN-L PLUG HSG	 TE Part # 172332-1 MINI UNIVERSAL MATE-N-LOK CAP HOUSING 9P	 TE Part # 1-172165-6 2CIR MINI U-M-N-L PLUG BLUE



TE Part # 1-172169-9
9 POS TR MINI UNIV



TE Part # 1-172332-9
MUMNL PM CAP 9P



TE Part # 172327-1
UNIV M-N-L HSG



TE Part # 172344-1
MINI UNIVERSAL MATE-N-LOK CAP HOUSING 3P



TE Part # 172343-1
MINI UNIVERSAL M-N-L HOUSING



TE Part # 1-172165-9
2CIR MINI U-M-N-L PLUG BLCK



TE Part # 1-172164-2
MINI UNIVERSAL M-N-L PLUG 1P



TE Part # 1-172330-9
UNIVERSAL MATE-N-LOK CAP 4P


Also in the Series | Mini-Universal MATE-N-LOK



Connector Contacts(89)



Connector Hardware(4)



PCB Headers & Receptacles(93)




Power Contacts(89)



Rectangular Connector Housings(104)



Rectangular Power Connectors(196)



Standard Rectangular Connectors(104)


Customers Also Bought




TE Part #800621-SF
FN2060-20-08




TE Part #35492
PG RING 12-10 1/4 STUD



TE Part #1-163083-1
.062 DIA SOC.ASS 3+



TE Part #9-683403-1
ANVIL, COMBINATION



Documents

Product Drawings

MINI UNIVERSAL M-N-L SOCKET

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_170362-3_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_170362-3_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_170362-3_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Crimping of Mini-Universal MATE-N-LOK Contact

Japanese

Application Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese



Mini-Universal MATE-N-LOK Connector

Japanese