



PRODUCT NUMBER	PITCH
EHxx21x000J0G	3.50 mm



Material:

- Item A Clamp: Brass(CuZn) Ni plated
- Item B Terminal screw: Steel Zinc plating: "—" slot type
- Item C Female contact: High conductivity copper
- Item D Terminal(housing): Thermoplastic (UL94 V-0)

Electrical

- Voltage rating: 150VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque(Lb-In): 1.1
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval: cULus

PART NO.: EH xx 21 x 0 00J0 G

N = Number of poles

Dim A=Nx3.5

Dim B=(N-1)x3.5

poles	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.25	±0.25
19-24p	±0.30	±0.25

End Stackable	No. of poles	Color	RoHS compliant
0	2	Black (RAL9005)	(lead<4%)
02	2 poles	Red (RAL3001/D)	In copper Alloy
03	3 poles	Orange(RAL2011/P)	
...	...	4 Yellow(RAL1018/A)	
24	24 poles	5 Green(RAL6018/T)	
		6 Blue (RAL5015/A)	
		8 Grey(RAL7035/D)	
		9 White(RAL1102)	
		C Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK						
ltr	ecn	no	dr	date		tolerances unless otherwise specified				title TERMINAL BLOCK						
						angles		linear	X.±0.5				PLUGGABLE,180D WIRE INLET,END STACKABLE			
						X.X±0.3										
						X*±1"			X.XX±0.1							
						dr	EVIN ZHONG	041614			dwg no		sheet 1 of 1		size	
						engr	EVIN ZHONG	041614			EHxx21x000J0G		A			
						chr	HANKE FENG	041614								
						appd	SHI JUN	041614								
sheet index		revision sheet		A	1											