






NOTES:

- 1- MATERIAL: PHOSPHOR BRONZE ALLOY C52100
- 2- FINISH:
 - (A) - SELECTIVE GOLD PLATE .000030/(0.00076)MIN., AND SELECTIVE TIN .000100/(0.00254) OVER .000050/(0.00127) NICKEL OVERALL.
 - (B) - .000100/(0.00254) TIN OVER .000050/(0.00127) NICKEL.
- 3- PRODUCT SPECIFICATION: TBD.
- 4- PACKAGING INFORMATION: SEE SHEET 2 FOR CHAIN
PK-5556-003 FOR LOOSE TERMINALS
- 5-FOR USE WITH ASSEMBLY NO. A-30490-0001.
- △-MEASURING POINT FOR PLATING THICKNESS.
- ▽ 7-TERMINAL CANNOT BE USED IN 42475 OR 43558 HOUSINGS.
- △ -GOLD PLATING AREA.
- △ -TIN PLATING AREA.



SECTION "A" - "A"
SCALE = 16:1



VIEW "B" - "B"
SCALE = 16:1

30490-9902	B	CHAIN	RIGHT TO LEFT (SEE SHT. 2)	4000	18-24
30490-9802	A	CHAIN	RIGHT TO LEFT (SEE SHT. 2)		
30490-2012	B	LOOSE			
30490-2002	B	CHAIN	LEFT TO RIGHT (SEE SHT. 2)	4000	18-24
30490-1012	A	LOOSE			
30490-1002	A	CHAIN	LEFT TO RIGHT (SEE SHT. 2)		
ITEM NO.	PLATING	FORM	UNREEL DIRECTION	QTY. PER REEL	WIRE GAGE REF.
AFTER PLATING					

CORRECTED NOTE 4
EC NO: UAU2011-0264
DRWN: JAGUILAR 2010/09/30
CHKD: APPR: MKNACK 2011/01/28
REV

QUALITY SYMBOLS
▽=0
▽=0
▽=2

GENERAL TOLERANCES (UNLESS SPECIFIED)

	mm	INCH
4 PLACES	± .005	± .0005
3 PLACES	± .005	± .0005
2 PLACES	± .005	± .0005
1 PLACE	± .005	± .0005

ANGULAR ± 5°

DRAFT WHERE APPLICABLE
MUST REMAIN
WITHIN DIMENSIONS

DIMENSION STYLE
IN/MM

DRAWN BY: BBW
DATE: 92/ 1/22

CHECKED BY: DATE:

APPROVED BY: MKNACK
DATE: 2011/01/28

MATERIAL NO.

SIZE: C

SCALE
8:1

DESIGN UNITS
INCH

THIRD ANGLE PROJECTION

CRIMP TERMINAL
MINI-FIT STYLE


MOLEX INCORPORATED

DOCUMENT NO.
SD-30490-*2**


SHEET NO.
1 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

LEFT TO RIGHT
UNREELING



RIGHT TO LEFT
UNREELING



RED FLANGE NO. 70180-0659
EDP NO. 85-06-0002
FOR (RED) 3 REEL CARTON
PART NO. 70180-0479
EDP NO. 85-01-0479

THIS IS SPECIAL PACKAGING -
ALL NON-AIRBAG CUSTOMERS
WILL USE STANDARD PACKAGING

DIMENSIONS SHOWN (METRIC) INCH		
UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 1/2°		
	INCH	METRIC
3 PLACE	± .005	---
2 PLACE	± .01	± 0.13
1 PLACE	---	± 0.25
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		
DRWG. BY APP'D. BY	BBW	CHK'D. BY SCALE :

▽ = 0		▼ = 0		REVISE ONLY ON CAD SYSTEM	
TITLE				CRIMP TERMINAL MINI-FIT STYLE	
MOLEX INCORPORATED LITSE,ILL. 60532 U.S.A.		SHEET NO. 2		DATE 92 / 1 / 22	
PART NO. 30490-***2		DRWG. NO. SD-30490-***2			
FILE NAME ST304902 DGN		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.			DIV. A SIZE C