
Your Expert Partner for **Human Machine Interfaces**

Switching element

71-672.026



https://www.eao.com/component/71-672.026/en/s...

Downloaded from Arrow.com.

Your product:



71-672.026
Switching element

ELECTRICAL CHARACTERISTICS

Contacts:	2 NC / 2 NO
Forward voltage:	
Switching rating:	250 V @ 3 A

MECHANICAL CHARACTERISTICS

Terminal:	PCB terminal
Contact material:	Gold
Switching system:	Snap-action switching element
Switching positions:	3 positions
Weight:	0.003 kg


CERTIFICATE

REACH:	REACH compliant
RoHS:	RoHS compliant


OTHER

Short Description:	Switching element, Snap-action switching element, 250 V @ 3 A, Gold, 2 NC / 2 NO, PCB terminal
Housing material:	Plastic, according to UL 94 V0
Product attributes:	Including locking pin
Hints:	Including locking pin
Wiring diagrams:	

Downloaded from Arrow.com.



Component layouts:



A = Terminals (rear side)
B = Drilling plan (component side)
C = non-metallic
D = Cu-Pad
E = Occupancy plan (component side)
F = 1. Switch
G = Switching element 2 Normaly close + 2 Normaly open, Part No. 71-672.026
H = 2. Switches
I = Switching element 1 Normaly close + 1 Normaly open, Part No. 71-671.026
J = Illumination element, Part No. 71-670.026
K = X1 Lamp cathode (-)
L = X2 Lamp anode (+)
M = 1-2 Contact normally closed
N = 3-4 Contact normally open
O = 5 Hole for interlocking pin
P = Front dimension min.
Q = Position interlocking pin
R = Note:
Pitch of the print circuit board hole Ø3.5 must agree with the mounting holes on the front plate
S = Slot in actuator

Downloaded from Arrow.com.