






HONEYWELL PART NUMBER
1SM36-H2
PRODUCT CODE TW-A3600
JG-80059

REV	DOCUMENT	CHANGED BY	CHECK
4	0058669	KNR 11NOV09	CMH



- NOTES:
- 1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF Ø.087 MAX ON .375±.002 CENTRES
 - 2 - TERMINALS ARE PLATED FOR SOLDERING
 - 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250°F
 - 4 - MINIMUM EXPECTED MECHANICAL LIFE 10,000 OPERATIONS

RELEASE NO.:
PR-18042
REPLACES
X91813-SM

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED:		DRAWN	JA	16OCT07	Honeywell				
OPERATING FORCE----- 4 OZ. MAX.		CONTACT ARRANGEMENT SPDT					CHECK	PSR	16OCT07					
RELEASE FORCE----- 1 OZ. MIN.		30 VOLTS DC RATING			NO PLACE X ± .040 ONE PLACE .X ± .030 TWO PLACE .XX ± .015 THREE PLACE .XXX ± .005 FOUR PLACE .XXXX ± .0005 ANGLES ± 2°		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH-BASIC				
DIFFERENTIAL TRAVEL----- .001 - .002														
OVERTRAVEL----- .010 MIN.														
							INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
					THIRD ANGLE PROJECTION		RASTER			B	I	1SM36-H2		4
														
										SCALE NONE		SHEET 1 OF 1		