






Material:

- Item ④ Male contact pin:Copper Tin plated
- Item ⑤ Terminal (housing): Thermoplastic (UL94V-0)

Electrical: cULus /VDE/TUV

- Voltage rating: 300V/300V/300V
- Current rating: 15A/17A/20A
- Withstanding Voltage: 1.6 KV/2.5KV/2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:   



PART NO.: VK xx 51 x 0 00J0 G

N = Number of poles
Dim A=(N-1)x5.08+6.48
Dim B=(N-1)x5.08

Solid block	0	Black (RAL9005)	RoHS compliant (lead<4%)
No. of poles	2	Red (RAL3001/D)	In copper Alloy
02 2 poles	3	Orange(RAL2011/P)	
03 3 poles	4	Yellow(RAL1018/A)	
... ..	5	Green(RAL6018/T)	
24 24 poles	6	Blue (RAL5015/A)	
	8	Grey(RAL 7035/D)	
	9	White(RAL1102)	
	C	Green(RAL6018/U)	

mat'l. code				surface ASME Y14.5		tolerance ASME Y14.5		projection 		product family TERMINAL BLOCK				
ltr ecn no dr date				tolerances unless otherwise specified						title				
				angles		TERMINAL BLOCK								
				X.±0.5										
				X.X±0.3				scale		PLUGGABLE SOCKET,CLOSE,45DEGREE INLET,WITHOUT FLANG				
				X*±1*		X.XX±0.1				dwg no		sheet 1 of 1		size
				dr EVIN ZHONG		042214				VKxx51x000J0G				A
				enrg EVIN ZHONG		042214								
				chr HANKE FENG		042214								
				appd SHI JUN		042214				type		CUSTOMER Drawin		
sheet index		revision sheet		A 1										